



Part Number : [2163002125](#)
Product Description : Pre-Crimped Lead
MX150 Female-to-MX150 Female, Tin (Sn)
Plating, 450.00mm Length, 14 AWG, Red
Series Number : 216300
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2163002125_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216300
Description	Pre-Crimped Lead MX150 Female-to-MX150 Female, Tin (Sn) Plating, 450.00mm Length, 14 AWG, Red
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MX150 Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	MX150
UPC	195842070554

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Net Weight	11.264/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	TXL
Wire Insulation Diameter	2.70mm max.
Wire Size (AWG)	14

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	<u>33472</u>
MX150 Mat-Sealed Single Row Female Connector Assemblies	<u>33471</u>
