




Part Number : [191930209](#)
Product Description : VersaKrimp Ring
Tongue Terminal for 6 AWG Wire, Closed-
Braided Barrel, Stud Size 10 (M5), Carton
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : E-357-10



Documents & Resources

Drawings
[191930209_sd.pdf](#)

3D Models and Design Files
[191930209_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	800755050592

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	6.270/g
Packaging Type	Carton
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	9.09mm max.
Wire Size (AWG)	6
Wire Size mm ²	16.00

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900004</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Square "DIN" style dies for 6 AWG	<u>640037770</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640074300</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>