




CKT SIZE	DIM A	DIM B
4	.709 (18.00)	.496 (12.60)
5	.874 (22.20)	.661 (16.80)
6	1.039 (26.40)	.827 (21.00)
7	1.205 (30.60)	.992 (25.20)
8	1.370 (34.80)	1.157 (29.40)
9	1.535 (39.00)	1.323 (33.60)
10	1.701 (43.20)	1.488 (37.80)
11	1.866 (47.40)	1.654 (42.00)
12	2.031 (51.60)	1.819 (46.20)



- NOTES:
- MATERIALS:
HOUSING:
1=NYLON 6/6, UL94 V-2, COLOR: NATURAL
2=NYLON 6/6, UL94 V-0, COLOR: NATURAL
3=NYLON 6/6, UL94 V-2, COLOR: BLACK
TERMINALS:
COPPER ALLOY
 - TERMINAL PLATING:
1=.000100/(0.00254) MIN. MATTE TIN OVER
.000050/(0.00127) MIN. NICKEL
2=.000030/(0.00076) MIN. SELECT GOLD AND
.000100/(0.00254) MIN. SELECT MATTE TIN
OVER .000050/(0.00127) MIN. NICKEL OVERALL
 - PRODUCT SPECIFICATION: PS-44476-001
 - PACKAGING: SEE CHARTS
 - PART MATES WITH MINI-FIT JR. RECEPTACLE NO. 5557.
 - PART IS NOT DESIGNED FOR CURRENT SHARING.
 - PARTS ARE NOT TO BE MATED OR UN-MATED WHILE CIRCUITS ARE LIVE.
 - 44472-2470 ONLY FOR WIDER LOCKING RAMP.
 - PARTS WILL HAVE "HCS" MARKING.
 - SEE CHART FOR PARTS WITH PEGS REMOVED.
 - PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.



LEGEND:

44472 - ** **


CIRCUIT SIZE
(04-12 FOR SINGLE ROW)
(02-24 FOR DUAL ROW)

ASSEMBLY VERSION
(01 THRU 49 FOR SINGLE ROW)
(50 THRU 99 FOR DUAL ROW)

SEE SHT. 2 FOR DUAL ROW

* THE CHART FOR SINGLE ROW PRODUCT IS ON PAGE 6.

CHANGE PLATING EC NO: UCP2012-1560 DRWN:NGUYEN 2012/01/05 CHKD:JBELL 2012/01/05 APPR:FSMTH 2012/02/02	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
						IN/MM		4:1	METRIC				
						DRAWN BY DATE		TITLE					
						CHECKED BY DATE		MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW					
						APPROVED BY DATE		MOLEX INCORPORATED					
						RJF 1994/07/25		SDA-44472-****					
						MATERIAL NO.		SEE CHARTS					
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		1 OF 8					
								THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



CIRCUIT SIZE	DIM. "A"	DIM. "B"	DIM. "C"
2	.21 (5.4)	—	.370 (9.40)
4	.38 (9.6)	.17 (4.2)	.535 (13.60)
6	.54 (13.8)	.33 (8.4)	.701 (17.80)
8	.71 (18.0)	.50 (12.6)	.866 (22.00)
10	.87 (22.2)	.66 (16.8)	1.031 (26.20)
12	1.04 (26.4)	.83 (21.0)	1.197 (30.40)
14	1.20 (30.6)	.99 (25.2)	1.362 (34.60)
16	1.37 (34.8)	1.16 (29.4)	1.528 (38.80)
18	1.54 (39.0)	1.32 (33.6)	1.693 (43.00)
20	1.70 (43.2)	1.49 (37.8)	1.858 (47.20)
22	1.87 (47.4)	1.65 (42.0)	2.024 (51.40)
24	2.03 (51.6)	1.82 (46.2)	2.189 (55.60)

SEE SHT. I FOR SINGLE ROW

SEE SHEET 1

EC NO: UCP2012-1560

2012/01/05

DRWN:NGUYEN

2012/01/05

CHKD:JBELL

2012/02/02

APPR:FSMITH

REV

QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .015
2 PLACES	± 0.38	± .020
1 PLACE	± 0.50	± ---

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

IN/MM

DRAWN BY

DATE

CHECKED BY

DATE

APPROVED BY

DATE

MATERIAL NO.

DOCUMENT NO.

SIZE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

4:1

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW

MOLEX INCORPORATED

SDA-44472-****

SHEET NO.

2 OF 8

	13	12	11	10	9	8	7	6	5	4	3	2	1	
	DUAL ROW PART NUMBERS WITH MATTE TIN PLATING													
J	WITH PEGS													J
	PLATING:	1 (SEE NOTE 2)			PLATING:	1 (SEE NOTE 2)			PLATING:	1 (SEE NOTE 2)				
	DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITH DRAIN HOLES				
	PEGS:	WITH PEGS			PEGS:	WITH PEGS			PEGS:	WITH PEGS				
	MAT'L:	94V-2 [NATURAL]			MAT'L:	94V-0 [NATURAL]			MAT'L:	94V-0 [NATURAL]				
	PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001				
I		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS		
		44472-0250		2		44472-0251		2		44472-0252		2		
		44472-0450		4		44472-0451		4		44472-0452		4		
		44472-0650		6		44472-0651		6		44472-0652		6		
		44472-0850		8		44472-0851		8		44472-0852		8		
		44472-1050		10		44472-1051		10		44472-1052		10		
H		44472-1250		12		44472-1251		12		44472-1252		12		
		44472-1450		14		44472-1451		14		44472-1452		14		
		44472-1650		16		44472-1651		16		44472-1652		16		
		44472-1850		18		44472-1851		18		44472-1852		18		
		44472-2050		20		44472-2051		20		44472-2052		20		
		44472-2250		22		44472-2251		22		44472-2252		22		
G		44472-2450		24		44472-2451		24		44472-2452		24		
	WITHOUT PEGS													
F	PLATING:	1 (SEE NOTE 2)			PLATING:	1 (SEE NOTE 2)			PLATING:	1 (SEE NOTE 2)			F	
	DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITH DRAIN HOLES				
	PEGS:	WITHOUT PEGS			PEGS:	WITHOUT PEGS			PEGS:	WITHOUT PEGS				
	MAT'L:	94V-2 [NATURAL]			MAT'L:	94V-0 [NATURAL]			MAT'L:	94V-0 [NATURAL]				
	PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001				
E		ITEM NO.	HOUSING NO.	CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS		
		44472-0254		2		44472-0255		2		44472-0256		2		
		44472-0454		4		44472-0455		4		44472-0456		4		
		44472-0654		6		44472-0655		6		44472-0656		6		
		44472-0854		8		44472-0855		8		44472-0856		8		
		44472-1054		10		44472-1055		10		44472-1056		10		
		44472-1254		12		44472-1255		12		44472-1256		12		
D		44472-1454		14		44472-1455		14		44472-1456		14		
		44472-1654		16		44472-1655		16		44472-1656		16		
		44472-1854		18		44472-1855		18		44472-1856		18		
		44472-2054		20		44472-2055		20		44472-2056		20		
		44472-2254		22		44472-2255		22		44472-2256		22		
		44472-2454		24		44472-2455		24		44472-2456		24		
C														
	* ITEMS PRECEDED BY AN *X* ARE NOT AVAILABLE.													
B														B
A														A
SEE SHEET 1 EC NO: UCP2012-1560 DRAWN: NGUYEN CHKD: J.BELL APPR: F.S.MITH M REV DESCRIPTION 2012/01/05 2012/01/05 2012/02/02 QUALITY SYMBOLS ▽=0 ▽=0 ▽=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .015 2 PLACES ± 0.38 ± .020 1 PLACE ± 0.50 ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE IN/MM DRAWN BY DATE GEP 1994/07/25 CHECKED BY DATE R.J.F. 1994/07/25 APPROVED BY DATE R.J.F. 1994/07/25 MATERIAL NO. SEE CHARTS SCALE 1:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW MOLEX INCORPORATED DOCUMENT NO. SDA-44472-**** SHEET NO. 3 OF 8 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	12	11	10	9	8	7	6	5	4	3	2	1		

	13	12	11	10	9	8	7	6	5	4	3	2	1																														
J	DUAL ROW PART NUMBERS WITH SELECT GOLD PLATING													J																													
	WITH PEGS																																										
	PLATING:	2 (SEE NOTE 2)			PLATING:	2 (SEE NOTE 2)			PLATING:	2 (SEE NOTE 2)			PLATING:	2 (SEE NOTE 2)																													
	DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITH DRAIN HOLES			DRAINS:	WITH DRAIN HOLES																													
	PEGS:	WITH PEGS			PEGS:	WITH PEGS			PEGS:	WITH PEGS			PEGS:	WITH PEGS																													
I	MAT'L:	94V-2 [NATURAL]			MAT'L:	94V-0 [NATURAL]			MAT'L:	94V-2 [NATURAL]			MAT'L:	94V-0 [NATURAL]																													
	PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001																													
		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS																											
	X	44472-0260		2	X	44472-0261		2		44472-0262		2	X	44472-0263		2																											
	X	44472-0460		4	X	44472-0461		4	X	44472-0462		4	X	44472-0463		4																											
	X	44472-0660		6	X	44472-0661		6	X	44472-0662		6	X	44472-0663		6																											
	X	44472-0860		8	X	44472-0861		8	X	44472-0862		8	X	44472-0863		8																											
H	X	44472-1060		10	X	44472-1061		10	X	44472-1062		10	X	44472-1063		10																											
	X	44472-1260		12	X	44472-1261		12	X	44472-1262		12	X	44472-1263		12																											
	X	44472-1460		14	X	44472-1461		14	X	44472-1462		14	X	44472-1463		14																											
	X	44472-1660		16	X	44472-1661		16	X	44472-1662		16	X	44472-1663		16																											
	X	44472-1860		18	X	44472-1861		18	X	44472-1862		18	X	44472-1863		18																											
	X	44472-2060		20	X	44472-2061		20	X	44472-2062		20	X	44472-2063		20																											
G	X	44472-2260		22	X	44472-2261		22	X	44472-2262		22	X	44472-2263		22																											
	X	44472-2460		24		44472-2461		24	X	44472-2462		24	X	44472-2463		24																											
F	WITHOUT PEGS													F																													
	PLATING:	2 (SEE NOTE 2)			PLATING:	2 (SEE NOTE 2)			PLATING:				PLATING:	2 (SEE NOTE 2)																													
	DRAINS:	WITHOUT DRAIN HOLES			DRAINS:	WITHOUT DRAIN HOLES			DRAINS:				DRAINS:	WITH DRAIN HOLES																													
	PEGS:	WITHOUT PEGS			PEGS:	WITHOUT PEGS			PEGS:				PEGS:	WITHOUT PEGS																													
	MAT'L:	94V-2 [NATURAL]			MAT'L:	94V-0 [NATURAL]			MAT'L:				MAT'L:	94V-0 [NATURAL]																													
E	PACKAGING:	PK-5566-001			PACKAGING:	PK-5566-001			PACKAGING:				PACKAGING:	PK-5566-001																													
		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS																											
	X	44472-0264		2	X	44472-0265		2				2	X	44472-0267		2																											
	X	44472-0464		4	X	44472-0465		4				4	X	44472-0467		4																											
	X	44472-0664		6	X	44472-0665		6				6	X	44472-0667		6																											
	X	44472-0864		8	X	44472-0865		8				8		44472-0867		8																											
	X	44472-1064		10	X	44472-1065		10				10	X	44472-1067		10																											
D	X	44472-1264		12	X	44472-1265		12				12	X	44472-1267		12																											
	X	44472-1464		14	X	44472-1465		14				14	X	44472-1467		14																											
	X	44472-1664		16	X	44472-1665		16				16	X	44472-1667		16																											
	X	44472-1864		18	X	44472-1865		18				18	X	44472-1867		18																											
	X	44472-2064		20	X	44472-2065		20				20	X	44472-2067		20																											
	X	44472-2264		22		44472-2265		22				22	X	44472-2267		22																											
C	X	44472-2464		24	X	44472-2465		24				24	X	44472-2467		24																											
	* ITEMS PRECEDED BY A "X" ARE NOT AVAILABLE.																																										
B														B																													
A														A																													
SEE SHEET 1 EC NO: UCP2012-1560 DRWN:NGUYEN CHKD:JBELL APPR:FSM1TH 2012/01/05 2012/01/05 2012/02/02 REV DESCRIPTION QUALITY SYMBOLS GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .015</td></tr><tr><td>2 PLACES</td><td>± 0.38</td><td>± .020</td></tr><tr><td>1 PLACE</td><td>± 0.50</td><td>± ---</td></tr><tr><td colspan="3">ANGULAR ±1/2°</td></tr></table> DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE IN/MM <table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>GEP</td><td>1994/07/25</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>RJF</td><td>1994/07/25</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>RJF</td><td>1994/07/25</td></tr></table> SCALE 1:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION TITLE MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW MOLEX INCORPORATED MATERIAL NO. SEE CHARTS DOCUMENT NO. SDA-44472-**** SHEET NO. 4 OF 8 SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .015	2 PLACES	± 0.38	± .020	1 PLACE	± 0.50	± ---	ANGULAR ±1/2°			DRAWN BY	DATE	GEP	1994/07/25	CHECKED BY	DATE	RJF	1994/07/25	APPROVED BY	DATE	RJF	1994/07/25
	mm	INCH																																									
4 PLACES	± ---	± ---																																									
3 PLACES	± ---	± .015																																									
2 PLACES	± 0.38	± .020																																									
1 PLACE	± 0.50	± ---																																									
ANGULAR ±1/2°																																											
DRAWN BY	DATE																																										
GEP	1994/07/25																																										
CHECKED BY	DATE																																										
RJF	1994/07/25																																										
APPROVED BY	DATE																																										
RJF	1994/07/25																																										

1b_frame_C_P_AM.T Rev. F 2009/06/18	12	11	10	9	8	7	6	5	4	3	2	1
--	----	----	----	---	---	---	---	---	---	---	---	---

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

13

12

11

10

9

8

7

6

5

4

3

2

1

DUAL ROW PART NUMBERS WITH WIDE LATCH OPTION

WITH PEGS

PLATING:	1 (SEE NOTE 2)
DRAINS:	WITH DRAIN HOLES
PEGS:	WITH PEGS
MAT'L:	94V-2 [NATURAL]
PACKAGING:	PK-5566-001

	ITEM NO.	CKTS
X	44472-0270	2
X	44472-0470	4
X	44472-0670	6
X	44472-0870	8
X	44472-1070	10
X	44472-1270	12
X	44472-1470	14
X	44472-1670	16
X	44472-1870	18
X	44472-2070	20
X	44472-2270	22
	44472-2470	24



* ITEMS PRECEDED BY *X* ARE NOT AVAILABLE.

SEE SHEET 1 EC NO: UCP2012-1560 2012/01/05 DRAWN: NGUYEN CHKD: J.BELL 2012/01/05 APPR: F.S.MITH 2012/02/02	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY GEP	DATE 1994/07/25	TITLE MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW			
			4 PLACES	± ---	± ---	CHECKED BY RJF	DATE 1994/07/25				
			3 PLACES	± ---	± .015	APPROVED BY RJF	DATE 1994/07/25	MOLEX INCORPORATED			
			2 PLACES	± 0.38	± .020	MATERIAL NO.					
			1 PLACE	± 0.50	± ---	SEE CHART		SDA-44472-****			
			ANGULAR ±1/2°			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
						SIZE C					

12

11

10

9

8

7

6

5

4

3

2

1

	13	12	11	10	9	8	7	6	5	4	3	2	1			
J	SINGLE ROW PART NUMBERS WITH PEGS													J		
I	MATTE TIN PLATING															
	PLATING: 1 (SEE NOTE 2)				PLATING: 1 (SEE NOTE 2)				PLATING: 1 (SEE NOTE 2)				PLATING: 1 (SEE NOTE 2)			
	DRAINS: WITH DRAIN HOLES				DRAINS: WITH DRAIN HOLES				DRAINS: WITHOUT DRAIN HOLES				DRAINS: WITHOUT DRAIN HOLES			
	PEGS: WITH PEGS				PEGS: WITH PEGS				PEGS: WITH PEGS				PEGS: WITH PEGS			
	MAT'L: 94V-2 [NATURAL]				MAT'L: 94V-0 [NATURAL]				MAT'L: 94V-2 [NATURAL]				MAT'L: 94V-0 [NATURAL]			
	PACKAGING: PK-5566-002				PACKAGING: PK-5566-002				PACKAGING: PK-5566-002				PACKAGING: PK-5566-002			
H	ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS	
	44472-040I		4	X	44472-0402		4	X	44472-0403		4	X	44472-0404		4	
X	44472-050I		5		44472-0502		5	X	44472-0503		5		44472-0504		5	
X	44472-060I		6	X	44472-0602		6	X	44472-0603		6	X	44472-0604		6	
X	44472-070I		7	X	44472-0702		7	X	44472-0703		7	X	44472-0704		7	
X	44472-080I		8	X	44472-0802		8	X	44472-0803		8	X	44472-0804		8	
X	44472-090I		9	X	44472-0902		9	X	44472-0903		9	X	44472-0904		9	
X	44472-100I		10	X	44472-1002		10	X	44472-1003		10	X	44472-1004		10	
G	X	44472-110I		11	X	44472-1102		11	X	44472-1103		11	X	44472-1104		11
X	44472-120I		12	X	44472-1202		12	X	44472-1203		12	X	44472-1204		12	
F	GOLD PLATING															
	PLATING: 2 (SEE NOTE 2)				PLATING: 2 (SEE NOTE 2)				PLATING: 2 (SEE NOTE 2)				PLATING: 2 (SEE NOTE 2)			
	DRAINS: WITHOUT DRAIN HOLES				DRAINS: WITHOUT DRAIN HOLE				DRAINS: WITHOUT DRAIN HOLES				DRAINS: WITHOUT DRAIN HOLES			
	PEGS: WITH PEGS				PEGS: WITH PEGS				PEGS: WITH PEGS				PEGS: WITH PEGS			
	MAT'L: 94V-2 [NATURAL]				MAT'L: 94V-2 [NATURAL]				MAT'L: 94V-2 [NATURAL]				MAT'L: 94V-0 [NATURAL]			
	PACKAGING: PK-5566-002				PACKAGING: PK-5566-002				PACKAGING: PK-5566-002				PACKAGING: PK-5566-002			
E	ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS		ITEM NO.		CKTS	
			4				4	X	44472-0407		4	X	44472-0408		4	
			5				5	X	44472-0507		5	X	44472-0508		5	
			6				6	X	44472-0607		6	X	44472-0608		6	
			7				7	X	44472-0707		7	X	44472-0708		7	
			8				8	X	44472-0807		8	X	44472-0808		8	
			9				9	X	44472-0907		9	X	44472-0908		9	
			10				10	X	44472-1007		10	X	44472-1008		10	
D			11				11	X	44472-1107		11	X	44472-1108		11	
			12				12	X	44472-1207		12	X	44472-1208		12	
C														C		
B														B		
A														A		
SEE SHEET 1 EC NO: UCP2012-1560 DRWN:NGUYEN 2012/01/05 CHKD:IBELL 2012/01/05 APPR:FSMITH 2012/02/02 M QUALITY SYMBOLS ▽ ⇒ ○ ▽ ⇒ ○ ▽ ⇒ ○ DESCRIPTION REV GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ±.000 ±.000 3 PLACES ±.000 ±.015 2 PLACES ±0.38 ±.020 1 PLACE ±0.50 ±.000 ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE IN/MM DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE MATERIAL NO. SIZE THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION SCALE 1:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION TITLE MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW MOLEX MOLEX INCORPORATED DOCUMENT NO. SDA-44472-**** SHEET NO. 6 OF 8																
	12	11	10	9	8	7	6	5	4	3	2	1				

1312

11

10

9

8

7

6

5

4

3

2

1

DUAL ROW PART NUMBERS WITH MATTE TIN PLATING
(DO NOT USE FOR NEW APPLICATIONS)

WITH PEGS			
PLATING:	1 (SEE NOTE 2)		
DRAINS:	WITH DRAIN HOLES		
PEGS:	WITH PEGS		
MAT'L:	94V-0 [NATURAL]		
PACKAGING:			
	ITEM NO.		CKTS
	44472-0283	0	2
	44472-0483	0	4
	44472-0683	0	6
	44472-0883		8
	44472-1083	0	10
	44472-1283	0	12
	44472-1483	0	14
	44472-1683	0	16
	44472-1883	0	18
	44472-2083		20
	44472-2283		22
	44472-2483	0	24

*0" = OBSOLETE

SEE SHEET 1 EC NO: UCP2012-1560 DRAWN:NGUYEN 2012/01/05 CHKD:JBELL 2012/01/05 APPR:FSMITH 2012/02/02	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
					IN/MM		1:1	METRIC			
				mm	INCH	DRAWN BY	DATE	TITLE MINI-FIT VERT HDR ASSY W & W/O PEGS/DRAIN HOLES SINGLE AND DUAL ROW			
			4 PLACES	± ---	± ---	GEP	1994/07/25				
			3 PLACES	± ---	± .015	CHECKED BY	DATE	MOLEX INCORPORATED			
			2 PLACES	± 0.38	± .020	RJF	1994/07/25				
			1 PLACE	± 0.50	± ---	APPROVED BY	DATE	DOCUMENT NO. SDA-44472-****			
			ANGULAR ±1/2°		RJF	1994/07/25					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SHEET NO.				
					SEE CHART		8 OF 8				
SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											