




Part Number : [190670092](#)
Product Description : NylaKrimp Funnel Entry
Ring Tongue Terminal for 2 AWG Wire, Stud
Size 3/8" (M9)
Series Number : 19067
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : G-974-38



Documents & Resources

Drawings
[190670092_sd.pdf](#)

3D Models and Design Files
[190670092_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)
[PS-19902-016-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9)
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753066694

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	23.135/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	15.24mm max.
Wire Size (AWG)	2

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192890010</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Hand Crimp Tool for 2 AWG Insulated Ring Terminals	<u>640017970</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>