

F

E

D

C

B

A

F


E

D

C


B

A



注記 NOTES

1. 使用材料 MATERIAL
- ハウジング POLYAMIDE46, GLASS FILLED, UL94V-0 (白)
 - アクチュエータ POLYPHENYLENE SULFIDE, GLASS FILLED, UL94V-0 (茶)
 - ターミナル PHOSPOR BRONZE
 - 金具 FITTING NAIL PHOSPOR BRONZE
- △ パターンはくり止め用金具
FITTING NAIL FOR PREVENTION OF PEELING OF P.C.B. PATTERN.
- △ ソルダータール半田付け面のスレ量、及び金具半田付け面のスレ量は、基準面 Y に対し上方向 0.05MAX. 下方向 0.2MAX. とし、相互のパラッキ量は、0.1MAX. とする。
- MISALIGNMENT OF SOLDER TAILS AND FITTING NAILS FROM Y
UPPER DIRECTION: 0.05 MAX., LOWER DIRECTION: 0.2 MAX.
MISALIGNMENT BETWEEN SOLDER TAILS AND FITTING NAILS: 0.1MAX.
- △ 偶数極に適用。
APPLY FOR EVEN CIRCUIT.
- △ 18極以上は2ヶ所、10~17極はハウジングセンター上に1ヶ所とする。
18 CKTS & MORE THAN 18 CKTS PLACED 2 POINT.
10~17 CKTS PLACED 1 POINT ON HOUSING CENTER.



19.6	15.5	15.3	14.5	52893-3095	52893-3019	30
18.6	14.5	14.3	13.5	-2895	-2819	28
17.6	13.5	13.3	12.5	-2695	-2619	26
16.6	12.5	12.3	11.5	-2495	-2419	24
15.6	11.5	11.3	10.5	-2295	-2219	22
15.1	11.0	10.8	10.0	-2195	-2119	21
14.6	10.5	10.3	9.5	-2095	-2019	20
13.6	9.5	9.3	8.5	-1895	-1819	18
12.6	8.5	8.3	7.5	-1695	-1619	16
12.1	8.0	7.8	7.0	-1595	-1519	15
11.6	7.5	7.3	6.5	-1495	-1419	14
11.1	7.0	6.8	6.0	-1395	-1319	13
10.6	6.5	6.3	5.5	-1295	-1219	12
10.1	6.0	5.8	5.0	-1195	-1119	11
9.6	5.5	5.3	4.5	-1095	-1019	10
8.6	4.5	4.3	3.5	52893-0895	52893-0819	8
D	C	B	(A)	EMBOSSD TAPE ORDER No. オダー番号	MATERIAL NO.	極数 CIRCUIT

注記 NOTES

6. 本製品は 52893-***17 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52893-***17.

REVISED
EC NO: J2016-0623
DRWN: SKITAZAWA 2015/12/11
CHKD: YKOBAYASHI 2016/02/15
APPR: KUSUHARA01 2016/02/17

DESCRIPTION
GENERAL TOLERANCES (UNLESS SPECIFIED)
0.25 UNDER UNDER ±0.03
0.25 OVER 0.5 UNDER ±0.05
0.5 OVER 1.0 UNDER ±0.1
1.0 OVER 10 UNDER ±0.2
10 OVER 30 UNDER ±0.25
30 OVER ±0.3
ANGULAR ±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

52893-***19 MODEL NO.
DIMENSION STYLE
MM ONLY
DRAWN BY
M. NAGATA
CHECKED BY
K. TOJO
APPROVED BY
M. SASAO
MATERIAL NO.
SIZE
A3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

DESIGN UNITS
METRIC
THIRD ANGLE
PROJECTION
0.5 FPC CONN ASSY ZIF
SMT RA BTM CONT E/O TYPE
-LEAD FREE-
molex
SD-52893-040
SHEET NO.
1 OF 2

10

9

8

7

6

5

4

3

2

1

F


E

D

C

B


A




参考基板レイアウト
RECOMMENDED P.C.BOARD
PATTERN DIMENSION (REF.)
(マウント面)
(MOUNTING SIDE)

注記 NOTES

- △ R0.3は、FPCの導体部にかからないこと。
R0.3 MUST NOT BE OVERLAPPED TO PATTERN OF FPC.



適合FPC推奨寸法
APPLICABLE FPC
RECOMMENDED DIMENSION
(仕上がり厚さ: 0.3 ±0.03)
(THICKNESS: 0.3 ±0.03)



適合FFC推奨寸法
APPLICABLE FFC
RECOMMENDED DIMENSION
(仕上がり厚さ: 0.3 ±0.03)
(THICKNESS: 0.3 ±0.03)

FPCについて:
打抜き方向は導体側から補強板側を推奨致します。
補強フィルム材質はポリイミドを推奨致します。
接着剤は熱硬化接着剤を推奨致します。

ABOUT FPC:
RECOMMENDED PUNCHER DIRECTION: FROM CONDUCTOR SIDE TO
STIFFENER BOARD SIDE.

RECOMMENDED MATERIAL:
STIFFENER FILM: POLYIMIDE
BONDING AGENT: THERMOSETTING BONDING AGENT

REVISED EC NO: J2016-0623 DRWN: SKITAZAWA 2015/12/11 CHKD: KOBAYASHI 2016/02/15 APPR: KUSUJHARA01 2016/02/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	52893-***19 MODEL NO. THIRD ANGLE PROJECTION	
		0.25 UNDER	UNDER	± 0.03	DRAWN BY	DATE	TITLE 0.5 FPC CONN ASSY ZIF SMT RA BTM CONT E/O TYPE -LEAD FREE-			
		0.25 OVER	0.5 UNDER	± 0.05	M. NAGATA	'04/01/09				
		0.5 OVER	1.0 UNDER	± 0.1	CHECKED BY	DATE				
		1.0 OVER	10 UNDER	± 0.2	K. TOJO	'04/01/09				
		10 OVER	30 UNDER	± 0.25	APPROVED BY	DATE				
		30 OVER		± 0.3	M. SASAO	'04/01/09				
		ANGULAR	±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				SEE SHEET 1		SD-52893-040		2 OF 2		
	D	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

9

8

7

6

5

4


3

2


1

注記 NOTES

- 製品詳細寸法については図面 SD-52893-040 を参照下さい。
RE DETAILED DIMENSION, SEE SD-52893-040
- 梱包数量：1000個/リール
NUMBER OF CONNECTORS：1000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH




- トップテープの剥離強度：0.1～1.3N/10 ～130gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1～1.3N/10 ～130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.



- 材料
キャリアテープ：ポリプロピレン (PP)
トップテープ：PET, PE, PEF
リール：ポリスチレン (PS) <リサイクル材を含む>

MATERIAL CARRIER TAPE:POLYPROPYLENE
TOP TAPE:PET,PE,PEF
REEL:POLYSTYRENE(PS)
<RECYCLE MATERIAL CONTAINED>

- 本製品は 52893-***90 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52893-***90



REVISED EC NO: J2016-0623 DRWN:SKITAZAWA 2015/12/11 CHKD:YKOBAYASHI 022016/02/15 APPR:TKUSUJHARA01 2016/02/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		0.25	UNDER	UNDER	± 0.03	DRAWN BY	DATE	TITLE 0.5 FPC CONN ASSY ZIF				
		0.25	OVER	0.5	UNDER	± 0.05	M.NAGATA					'04/01/09
		0.5	OVER	1.0	UNDER	± 0.1	CHECKED BY	DATE	-LEAD FREE- molex			
		1.0	OVER	10	UNDER	± 0.2	K.TOJO	'04/01/09				
		10	OVER	30	UNDER	± 0.25	APPROVED BY	DATE	DOCUMENT NO. SD-52893-041			
		30	OVER		± 0.3	MATERIAL NO.		SHEET NO. 1 OF 2				
	ANGULAR ±3 °				ENTER PART							
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

F

E

D

C

B

A

F




E

D

C

B

A



32	37.4	33.4	21.6	19.9	16.1	15.9	52893-3095	30
			20.6	18.9	15.1	14.9	△ -2895	28
			19.6	17.9	14.1	13.9	-2695	26
			18.6	16.9	13.1	12.9	-2495	24
			17.6	15.9	12.1	11.9	-2295	22
24	29.4	25.4	17.1	15.4	11.6	11.4	-2195	21
			16.6	14.9	11.1	10.9	-2095	20
			15.6	13.9	10.1	9.9	-1895	18
			14.6	12.9	9.1	8.9	-1695	16
			14.1	12.4	8.6	8.4	-1595	15
			13.6	11.9	8.1	7.9	-1495	14
			13.1	11.4	7.6	7.4	-1395	13
			12.6	10.9	7.1	6.9	-1295	12
			12.1	10.4	6.6	6.4	▽ -1195	11
			11.6	9.9	6.1	5.9	-1095	10
キャリアテープ幅 CARRIER TAPE WIDTH	F	E	(D)	(C)	(B)	(A)	52893-0895	8
MATERIAL NO.							極数 CIRCUIT	

REVISED EC NO: J2016-0623 DRWN:SKITAZAWA 2015/12/11 CHKD:YKOBAYASHI 02/20/15 APPR:TKUSUHARA01 2016/02/17	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		0.25 UNDER	UNDER	±0.03	DRAWN BY	DATE	TITLE 0.5 FPC CONN ASSY ZIF				
		0.25 OVER	0.5 UNDER	±0.05	M.NAGATA	'04/01/09					
		0.5 OVER	1.0 UNDER	±0.1	CHECKED BY	DATE	-LEAD FREE-				
		1.0 OVER	10 UNDER	±0.2	K.TOJO	'04/01/09					
		10 OVER	30 UNDER	±0.25	APPROVED BY	DATE	molex				
		30 OVER		±0.3	MATERIAL NO.						
		ANGULAR ±3 °			ENTER PART		SD-52893-041		2 OF 2		
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				