



- 注)
NOTES:
1. 材質
MATERIAL
黄銅 (板厚: 0.3)
BRASS (THICKNESS : 0.3)
 2. メッキ仕様
TERMINAL PLATING
接点部 : 金メッキ 0.1μmMIN.
CONTACT AREA : GOLD 0.1 MICROMETER MINIMUM.
 : パラジウムニッケルメッキ 0.6μmMIN.
 : PD-NI 0.6 MICROMETER MINIMUM.
圧着部 : 錫メッキ 1.0μmMIN.
CRIMP AREA : TIN 1.0 MICROMETER MINIMUM.
下地メッキ : ニッケルメッキ 1.5μmMIN.
UNDER PLATE : NICKEL 1.5 MICROMETER MINIMUM.
 3. 適用電線範囲 : UL1015, UL1865, AWG #16~14
APPLICABLE WIRE RANGE : UL1015, UL1865, AWG #16~14
 4. 被覆外径 : φ3.8MAX.
INSULATION EXTERNAL DIA : φ3.8MAX.
 5. 50638-9028 は 50638-9049 の鉛フリー品である。
50638-9128 は 50638-9149 の鉛フリー品である。
50638-9028 IS LEAD FREE OF 50638-9049.
50638-9128 IS LEAD FREE OF 50638-9149.

バラ状 LOOSE	50638-9128
連鎖状 CHAIN	50638-9028
端子形状 TERMINAL CONFIGURATION	MATERIAL NO.

164NO. DRWN: CH'K: APPR:		163NO. DRWN: CH'K: APPR:		162NO. DRWN: CH'K: APPR:		161NO. DRWN: CH'K: APPR:		新規作成 RELEASED 160NO. J2004-4129 DRWN: M.NAGATA '04/05/10 CH'K: K.TOJO '04/05/10 APPR: M.SASAO '04/05/10		DESCRIPTION REV	MATERIAL 材料		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE 5:1	DESIGN UNITS mm INCH	2889RD ANGLE PROJECTION	DIMENSIONS: mm INCH		TITLE: 2mm PITCH AC/DC CONN. PLUG CRIMP TERM. (MII DRAWER CONNECTOR) -LEAD FREE-															
								0	FINISH 仕上り				10 UNDER 未満	±0.2																					
													10 OVER 以上	±0.25	30 UNDER 未満																				
											WIRE RANGE 適用電線範囲																								
											INS. RANGE 被覆外径																								
													ANGLE 角度		±3°				CAD FILENAME SD-50638-001.S01		MATERIAL NO. SEE CHART		DRAWING NO. SD-50638-001		SHEET NO. 1 OF 1										