






4.5	4.97	4.18	5.5	3.5	501461-0801	501461-0809	8
4.0	4.47	3.68	5.0	3.0	NOT AVAILABLE	NOT AVAILABLE	7
3.5	3.97	3.18	4.5	2.5	501461-0601	501461-0609	6
3.0	3.47	2.68	4.0	2.0	501461-0501	501461-0509	5
2.5	2.97	2.18	3.5	1.5	501461-0401	501461-0409	4
E	D	C	B	A	エンボス梱包品 EMBOSSED PACKAGING	製品番号 MATERIAL NO.	極数(N) CIRCUITS(N)

REVISED	EC NO: J2006-2218	2006/01/10	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
	DRWN:RSUMIYA	2006/01/11		10 UNDER	±0.2	DRAWN BY RSMIYA	DATE 2004/11/10	TITLE 0.5 FPC CONN BACK FLIP HGT=0.8 HSG ASSY -LEAD FREE-				
	CHKD:HHIRATA	2006/01/11		10 OVER 30 UNDER	±0.25	CHECKED BY HHIRATA	DATE 2004/11/10					
	APPR:HHIRATA	2006/01/11		30 OVER	±0.3	APPROVED BY MSASAO	DATE 2004/11/10	MOLEX INCORPORATED				
				ANGULAR	±1	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-501461-001		1 OF 2		
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



推奨基板寸法
RECOMMENDED P.C.BOARD PATTERN LAYOUT



推奨FPC寸法
RECOMMENDED FPC PATTERN LAYOUT




FPCについて:
抜き方向は、導体側から補強板側を推奨します。
補強フィルム材質は、ポリイミドを推奨します。
接着剤は、熱硬化接着剤を推奨します。
尚、接着剤の接点部への付着は、導通不良の原因となりますので染み出しが無いよう、お願いします。

ABOUT FPC:
RECOMMENDED PUNCHER DIRECTION :
FROM CONDUCTOR SIDE TO STIFFNER FILME SIDE.
RECOMMENDED MATERIAL :
STIFFNER FILME : POLYIMIDE
BONDING AGENT : THRMOSSETTING AGENT
PLEASE PUT APPROPRIATE AMOUNT OF ASHESIVE MAY CAUSE
THE DEFECT IN ELECTRICAL CONTINUITY.

REVISED		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
EC NO: J2006-2218	2006/01/10	10 UNDER	± 0.2	DRAWN BY	DATE	10:1	METRIC	0.5 FPC CONN BACK FLIP HGT=0.8 HSG ASSY -LEAD FREE-	
DRWN:RSUMIYA	2006/01/11	10 OVER 30 UNDER	± 0.25	CHECKED BY	DATE				
CHKD:HHIRATA	2006/01/13	30 OVER	± 0.3	APPROVED BY	DATE			MOLEX INCORPORATED	
APPR:HHIRATA	2006/01/13	ANGULAR	± 1	MSASAO	2004/11/10				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				SEE CHART		SD-501461-001		2 OF 2	
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			


引き出し方向
PULL OUT DIRECTION

REEL



NOTES

- 製品詳細寸法については製品単体図面を参照下さい。
RE DETAILED DIMENSION, SEE PRODUCT DRAWING.
- 梱包数量: 3000個/リール
NUMBER OF CONNECTORS 3000PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH




- トップテープの剥離強度: $0.1N \sim 1.3N$ { $10gf \sim 130gf$ }
(剥離強度は下図参照)

尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)

PEELING OFF FORCE OF TOP TAPE : $0.1N \sim 1.3N(10gf \sim 130gf)$
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)

THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.



- 材料

MATERIAL

キャリアテープ(CARRIRE TAPE): ポリスチレン (POLYSTYRENE)

トップテープ(TOP TAPE): PET, PE, PEF

リール(REEL): ポリスチレン (PS) <リサイクル材を含む>

POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAILED>

REVISED		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: J2006-2822		10 UNDER		MM ONLY		---		METRIC		◎ □	
2006/03/08	DRW:RSUMIYA	10 OVER	± 0.2	DRAWN BY	DATE	TITLE		501461-**01		MODEL NO.	
2006/03/08	CHKD:HHIRATA	30 UNDER	± 0.25	CHECKED BY	DATE						
2006/03/10	APPR:HHIRATA	30 OVER	± 0.3	APPROVED BY	DATE						
		ANGULAR	$\pm 1^\circ$	MSASAO	2005/02/07	MOLEX INCORPORATED		SD-501461-002		1 OF 2	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		DOCUMENT NO.		SHEET NO.			
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
				A3							

