

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528921833

Status:

Active

Overview:

FFC-FPC (SMT)

Description:

0.50mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, Cable Retention Guide, 18 Circuits

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-52892-040-001 \(PDF\)](#)
- [Packaging Specification SPK-52892-001-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Comments

Overview

Product Name

UPC

FFC/FPC Connectors

52892

Hinge, Cable Guide, Hinge, Cable Guide

FFC-FPC (SMT)

Easy-On

887191274126

Physical

Actuator Type

Circuits (Loaded)

Color - Resin

Contact Position

Durability (mating cycles max)

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire/Cable Type

Flip

18

Natural

Bottom

20

2.00mm

Phosphor Bronze

Tin-Silver-Bismuth

Tin-Silver-Bismuth

Nylon

205.312/mg

1

Right Angle

2.00mm

No

Surface Mount

Yes

Embossed Tape on Reel

0.50mm

0.50mm

No

No

N/A

-40° to +85°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

50V

Material Info

Reference - Drawing Numbers

Packaging Specification


Product Specification

Sales Drawing

SPK-52892-001-001

PS-52892-040-001

SD-52892-044, SD-52892-045



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

52892 Series

This document was generated on 03/28/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION