

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5034800400

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, FBH1 Series, Right-Angle, Dual Contact, 1.00mm Height, 4 Circuits, Gold over Nickel Plating



Series image - Reference only

Documents:

- [Drawing \(PDF\)](#)[Datasheet \(PDF\)](#)
- [3D Model \(PDF\)](#)[Product Guide \(PDF\)](#)
- [3D Model](#)[RoHS Certificate of Compliance \(PDF\)](#)
- [Product Specification PS-503480-001 \(PDF\)](#)[Reference Guide \(PDF\)](#)
- [Packaging Specification SPK-503480-001-001 \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Comments

Overview

Product Name

Series Name

UPC

FFC/FPC Connectors

503480

Black Actuator

Easy-On FFC FPC Connectors

Easy-On

FBH1

884982040823

Physical

Actuator Type

Circuits (Loaded)

Color - Resin

Contact Position

Durability (mating cycles max)

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to PCB

Stackable

Temperature Range - Operating

Wire/Cable Type

Flip

4

Natural (White)

Dual

10

94V-0

1.00mm

Phosphor Bronze

Gold

Gold

Liquid Crystal Polymer

21.781/mg

1

Right Angle

No

Surface Mount

Yes

Embossed Tape on Reel

0.50mm

Yes

No

-40° to +85°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

50V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

003

REFLOW

002

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series
503480 Series

Process Temperature max. C	250
Material Info	
Reference - Drawing Numbers	
Packaging Specification	SPK-503480-001-001
Product Specification	PS-503480-001
Sales Drawing	SD-503480-001, SD-503480-002

This document was generated on 03/09/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION