



Part Number : [1200878244](#)
Product Description : Nano-Change (M8)
Double-Ended Cordset with Knurled Hexnut,
5 Poles, B-Coded, Male (Straight) to Female
(90°), 24 AWG, Black PVC Cable, 5.0m (16.40')
Length
Series Number : 120087
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 445031E02M050



Documents & Resources

Drawings
[1200878244_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Female (90°), 24 AWG, Black PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Double Ended
UPC	78172511678

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Cable Diameter	5.30mm (.209")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
Coupling Style	Threaded
Gender	Female-Male
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass

Material - O-Ring	FKM
Material - Plating Mating	Gold
Net Weight	221.802/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	24

This document was generated on Feb 26, 2025