



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: **Enables Zhaga Compatibility, Not Optic Compatible**

Operating Voltage: **300 VDC**

Termination Method to Wire & Cable: **Poke-In**

Features

Product Type Features

LED Holders Product Type	LED Holder
--------------------------	------------

Configuration Features

Lighting Connector Features Included	Enables Zhaga Compatibility, Not Optic Compatible
--------------------------------------	---

Electrical Characteristics

Current Rating (Max)	5 A
Operating Voltage	300 VDC

Contact Features

Contact Mating Area Plating Material	Silver (Ag)
Contact Base Material	Copper Alloy

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Housing Features

Housing Material	PBT GF
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | LUMAWISE LED Holders




LED Holders(70)

Customers Also Bought



TE Part #4-1879350-2
RR01 5% 11R AMMO



TE Part #1623804-8
SQZ10 3R3 5% WIRE



TE Part #1-440055-1
2.0MM,HDR,11POS,R/A



TE Part #TAA545B1411-060
M12A4-MS-FS-PVC-6.0M






TE Part #1-1415899-8
[RZ03-1A4-D048](#)



TE Part #4-2176414-8
[7W STD M/OX 5% 1K8](#)



TE Part #8-2176407-8
[3560 27R 5%](#)



TE Part #8-1419125-5
[SDT-S-106LMR,000](#)



TE Part #1-1393250-7
[W28-XQAT-15=W28](#)

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_2213134-1_3.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2213134-1_3.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213134-1_3.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773700-5_LED_Holder_Type_LUXEON_K_Z50](#)

English

[1-1773702-2_Z50PHILLIPS_COB](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CB_CERT_IEC_60838-2-2_NL-42967_C1](#)

English

