



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: **Enables Zhaga Compatibility, Optic Compatible**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

LED Holders Product Type	Z50 Optic Clip
--------------------------	----------------

Configuration Features

Lighting Connector Features Included	Enables Zhaga Compatibility, Optic Compatible
--------------------------------------	---

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



	Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2213401-2
LUMAWISE LED HOLDER Z50 STD
PROFILE 1818



TE Part # 2213407-2
LUMAWISE LED HOLDER Z50 STD
PROFILE 2424

Also in the Series | LUMAWISE LED Holders



LED Holders(70)

Customers Also Bought



TE Part #1776293-3
TSB23003DS=EUROPA TERM BLK,
8MM



Documents

Product Drawings

LUMAWISE LED HOLDER OPTIC CLIP Z50 TYPE2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213349-1_A_c-2213349-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213349-1_A_c-2213349-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213349-1_A_c-2213349-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English