




PLASTI-GRIP

TE Internal #: 328527

Closed Ring Tongue Terminal, 16 – 14 AWG, #8 / M4 Stud, 4.34 mm [.171 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PLASTI-GRIP

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 2050 – 5180 CMA

Stud Size: #8, M4

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No

Wire Insulation Support Retention Type	Insulation Support
--	--------------------

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Product Weight	.796 g
Insulation Sleeve Color	Blue
Stripe Color	Blue

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight



Terminal Plating Material	Tin
---------------------------	-----

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	4.34 mm [.171 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	20.96 mm [.825 in]
Compatible Insulation Diameter (Max)	4.9 mm [.193 in]
Compatible Insulation Diameter Range	3 – 4.9 mm [.118 – .193 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 47807-1 DIES PIDG 16-14 DIE SET	 TE Part # 58423-1 DIE, RBY IS9252	 TE Part # 59170 T-HEAD PIDG SH 26-14 ASSY
 TE Part # 2392022-2 BLUE BATTERY DAHT KIT 220V (47387-7)	 TE Part # 169400 CERTI-LOK FRAME W/O DIES	 TE Part # 47387 DAHT PG PIDG 20-14 ASSY	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY
 TE Part # 525691 DAHT PG PIDG 16-14 ASSY	 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 2392022-1 BLUE BATTERY DAHT KIT 110V (47387-7)	 TE Part # 1-47387-0 DAHT PIDG PG 16-14 HEAD



TE Part # 47387-7
DAHT PG PIDG 16-12 ASSY

TE Part # 2063030-1
SDE DIESET, RBY, UL

TE Part # 539691-2
ERGO DIE R.B.Y

TE Part # 169404
CERTI-LOK DIE

Also in the Series | **PLASTI-GRIP**

Compression Connectors(3)

Crimp Wire Pins, Tabs & Ferrules(20)

Ring Terminals(310)

Spade Terminals(159)

Splices(45)

Customers Also Bought

TE Part #53440-1
ELECTRO-TAP, 18-14 AWG RUN&TAP

TE Part #53440-2
ELECTRO-TAP, 20-18 AWG RUN&TAP

TE Part #281783-8
PLUG HE14 IDC 180 8 P AWG 26-24


TE Part #1SNA116302R2300
MB10/22.SF

TE Part #3-1393118-0
KUP-14D35F-24=KU

TE Part #34243
PG BUTT SPLC 22-16COMM22-18MIL

TE Part #4-1415899-7
RZ03-1A3-D005

TE Part #350669-1
UMNL GRND PIN 20-14 PTPBR L/P



Documents

Product Drawings

TERMINAL,PG R 16-14 8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_328527_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_328527_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_328527_J.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_328527_H1.2d_dxf.zip

English

Customer View Model

ENG_CVM_328527_H1.3d_igs.zip

English

Customer View Model

ENG_CVM_328527_H1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English

328527

Closed Ring Tongue Terminal, 16 – 14 AWG, #8 / M4 Stud, 4.34 mm [.171 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PLASTI-GRIP



UL Report

English