



DATA SHEET


Model No.: GP80AAAHCL

Type	: Rechargeable Nickel Metal Hydride Prismatic Batteries
Nominal Dimension (with Sleeve)	: $\Phi = 10.5\text{mm}$ H = 44.5mm
Applications	: Recommended discharge current 80 to 2400mA
Nominal Voltage	: 1.2V
Capacity	: Rated: 800mAh Typical: 850mAh When discharged at 160mA to 1.0V at 20°C
Charging Condition	: 80mA for 16 hrs at 20°C
Charging Retention	: 70% of nominal capacity after cell storage at 20°C for 12 months When discharged at 160mA to 1.0V at 20°C
Fast Charge	: 400mA to 800mA (0.5 to 1C) charge termination control recommended control parameters: - ΔV : 0-5mV DT/dt : 0.8°C/min (0.5 to 0.9C) 0.8 - 1°C/min (1C) TCO : 45 - 50°C Timer : 105% nominal input (for ref. only)
Service Life	: >200 cycles (IEC61951-2(2017)-7.5.1.2) >50 cycles (IEC61951-2(2017)-7.5.1.4) >500 cycles (refer to GP product specification)
Continuous Overcharge	: 80mA maximum current for 1 year. No conspicuous deformation and/or leakage
Weight	: 13.4g
Internal Resistance	: Average 40m Ω upon fully charged (Max. 60 m Ω) at 1000Hz
Max. Charge Voltage	: 1.5V at 80mA charging
Ambient Temperature Range	: Charging: 0 to 45°C Fast Charging: 10 to 55°C Discharging: -20 to 50°C Storage: -20 to 35°C




Unit: mm


High Rate Discharge



Low Rate Discharge



Fast Charge (Charge Control Required)



The above information is generally descriptive only and is not intended as guarantee or warranty. Cell and battery specifications are subject to change without notice. All descriptions or warranties are contained solely in specification sheets accompanying outside those described in this document.

MRS6452 rev.00