



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 202 – 810 CMA

Stud Size: #6, M3.5

Features

Product Type Features

|                            |                             |
|----------------------------|-----------------------------|
| Ring Terminal Product Type | Closed Ring Tongue Terminal |
| Stud Size                  | #6, M3.5                    |
| Sealable                   | No                          |

|                                        |                        |
|----------------------------------------|------------------------|
| Wire Insulation Support Retention Type | Non-Insulation Support |
|----------------------------------------|------------------------|

Configuration Features

|                 |   |
|-----------------|---|
| Number of Holes | 1 |
|-----------------|---|

Body Features

|                |        |
|----------------|--------|
| Product Weight | .128 g |
|----------------|--------|

Contact Features

|                           |          |
|---------------------------|----------|
| Barrel Type               | Closed   |
| Terminal Orientation      | Straight |
| Terminal Plating Material | Tin      |

Mechanical Attachment

|                         |         |
|-------------------------|---------|
| Wire Insulation Support | Without |
|-------------------------|---------|

Dimensions

|                        |                  |
|------------------------|------------------|
| Wire Size              | 202 – 810 CMA    |
| Stud Diameter          | 3.51 mm[.138 in] |
| Tongue Thickness       | .51 mm[.02 in]   |
| Product Length         | 11.43 mm[.45 in] |
| Barrel Inside Diameter | .89 mm[.035 in]  |

Usage Conditions

|                   |             |
|-------------------|-------------|
| Insulation Option | Uninsulated |
|-------------------|-------------|

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |

Industry Standards

|                               |    |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 1000 |
| Packaging Method   | Box  |

Other

|      |        |
|------|--------|
| Line | Budget |
|------|--------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



REPRESENTATION ONLY

TE Part # 69363  
DAHT STRATO SOLIS 26-20 ASSY


Also in the Series | SOLISTRAND Budget



Knife Disconnects(4)



Ring Terminals(106)



Spade Terminals(46)

Customers Also Bought



TE Part #1-2118651-0  
RF CA,UMCC GEN1-GEN1,1.13MM CABLE,L60MM



TE Part #5745854-3  
CABLE CLAMP KIT,SZ 1




TE Part #D369-P66-BP0  
369 6 WAY PLUG, NO CONTACTS, PIN



TE Part #2-6609107-6  
PS0SXS30=C1061



TE Part #D369-R66-NS0  
369 6 WAY REC, NO CONTACTS, SKT



TE Part #5-1123723-4  
3.96 EP HDR ASSY 4P(BLACK)



TE Part #2329383-4  
PB OFF/ON FC GRE M1 TERM. IP68



TE Part #YDTS24H15-35ZN0000  
HERM RECP ASSY



TE Part #YDTS24H13-35ZN0000  
HERM RECP ASSY



TE Part #RJ45-ECS  
RJ45,ECS,12in

Documents

Product Drawings

TERMINAL,BUDG R 26-22 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_31430\_KU.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_31430\_KU.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_31430\_KU.3d\_stp.zip

English

3D PDF

English

Customer View Model

ENG\_CVM\_31430\_O.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_31430\_O.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_31430\_O.2d\_dxf.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.