

PART No MATRIX

9

9 = M12
SINGLE ENDED
2xKEYWAY

0

0=Portable

3

POLES:
3 = 3 POLES

0

HEADER:
006 = MALE STRAIGHT

0

6

X

CABLE:
E11 = PVC, 3x0,34mm²,
YELLOW
I12 = PVC, 3x0,50mm²,
GREY
I14 = PVC, 3x1,00mm²,
GREY
D02 = PVC, 3x1,20mm²,
YELLOW

X

X

M

UNIT:
M = METER

*

LENGTH:
EXAMPLE:
010 = 1 m
050 = 5 m
100 = 10 m

*


*

*


COUPLIN NUT:
BLANK = NYLON
3 = NICKEL PLATED BRASS
OVERMOULD:
BLANK = YELLOW

*

*



WIRING DIAGRAM
GREEN/YELLOW
BLUE
BROWN



VIEW FROM THE FRONT SIDE

BILL OF MATERIAL

7	2	ID CARRIER	PVC	-
6	1	LABEL WRAP	VINYL	YELLOW
5	1	COUPLING NUT MALE M12	ELECTROPHORETIC	BLACK
4	3	CONTACT 10 MA	BRONZE	GOLD OVER NICKEL PLATED
3	1	INSERT 3P MALE	NYLON	BLACK
2	-	MOULDING MATERIAL	POLYVINYL	YELLOW
1	-	CABLE 3X0.34MM	SEE CABLE INFORMATION - SHEET 2	
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH/COLOR

DOCUMENT STATUS	P1	RELEASE DATE	2021/03/16	13:03:08
-----------------	----	--------------	------------	----------

NOTES:

1. FOR CABLES "Ixx" - ID-CARRIES ON THE BOTH SIDES OF HARNESS
2. FOR CABLES "Ixx" PRINGING - ENGINEERING No

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

2:1

GENERAL TOLERANCES
(UNLESS SPECIFIED)

ANGULAR TOL ± °

4 PLACES ±

3 PLACES ±

2 PLACES ±

1 PLACE ±

0 PLACES ±

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

CURRENT REV DESC: OBSOLETE PART NUMBER

EC NO: 655037
DRWN: VLOKESHA
CHK'D: GGA
APPR: GGA

2020/12/22
2021/03/16
2021/03/16

INITIAL REVISION:
DRWN: MKOWALCZYK01
APPR: MIWASIECZKO

2018/09/27
2018/10/01

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

120072

DOCUMENT NUMBER

1200728076

MATERIAL NUMBER

SEE SHEET 2

CUSTOMER

GENERAL MARKET

DOC TYPE

PSD

DOC PART

000

REVISION

A2

SHEET NUMBER

1 OF 2

FORMAT: master-b-prod-A3
REVISION: 3
DATE: 2020/01/14

