



Part Number : [5037630691](#)
Product Description : 1.00mm Pitch, Pico-Lock
PCB Header, Single Row, Right-Angle, Surface
Mount, Gold over Nickel Plating, Positive Lock,
6 Circuits, Tape and Reel
Series Number : 503763
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources

Drawings
[5037630691_sd.pdf](#)

3D Models and Design Files
[5037630691.dxf](#)
[5037630691.pdf](#)
[5037630691_stp.zip](#)

Specifications
[AS-503764-001-001.pdf](#)
[SPK-503763-001-001.pdf](#)
[5037641001-PS-000.pdf](#)
[PS-503764-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	503763
Description	1.00mm Pitch, Pico-Lock PCB Header, Single Row, Right-Angle, Surface Mount, Gold over Nickel Plating, Positive Lock, 6 Circuits, Tape and Reel
Application	Signal, Wire-to-Board
Comments	See Molex product specification PS-503764-001 for additional current de-rating information
Component Type	PCB Header
Product Name	Pico-Lock
UPC	191128847063

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	150V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6

Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Mated Height	1.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	105.920/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.100µm
Polarized to Mating Part	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.00mm Pitch, Pico-Lock Single Row Receptacle Housings	<u>503764</u>