




Part Number : [877159005](#)
Product Description : 1.00mm Pitch, PCI Express Connector, 36 Circuits, Nylon 4/6 Glass-filled, Black Housing, Phosphor Bronze, 0.38µm Gold Solder-tail, Lead-Free
Series Number : 87715
Status : Active
Product Category : Card Edge Connectors



Documents & Resources

Drawings
[877159005_sd.pdf](#)
[PK-87715-001-001.pdf](#)
[PK-87715-207-001.pdf](#)

3D Models and Design Files
[877159005_stp.zip](#)
[EE-87715-004-001.pdf](#)
[EE-87715-011-001.pdf](#)
[EE-87715-012-001.pdf](#)
[EE-87715-013-001.pdf](#)
[EE-87715-014-001.pdf](#)
[SP-87715-004-001.zip](#)
[SP-87715-011-001.zip](#)
[SP-87715-012-001.zip](#)
[SP-87715-013-001.zip](#)
[SP-87715-014-001.zip](#)

Specifications
[PS-87715-200-001.pdf](#)
[TS-87715-207-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Card Edge Connectors
Series	87715
Description	1.00mm Pitch, PCI Express Connector, 36 Circuits, Nylon 4/6 Glass-filled, Black Housing, Phosphor Bronze, 0.38µm Gold Solder-tail, Lead-Free
Comments	PCI 1 lane
Component Type	Edge-card to PCB
Product Name	PCI Express
Standard Based	PCIe
UPC	822348679829

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.1A
-------------------------------	------

Data Rate	8.0 Gbps
High Power Bay (30.0A or more)	No
Voltage - Maximum	50V AC (RMS)/DC

Physical

Circuit Size Range	1-64 Circuits
Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Durability (mating cycles max)	50
Edge Card Thickness	1.57mm
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.867/g
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	3.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
(p)ower-(s)ignal Configuration	36s - 0p
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	WAVE
Max-Temp	245

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	PCI Express Card