


	10	9	8	7	6	5	4	3	2	1
F	MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER ON TAPE	ENGINEERING NUMBER ON TAPE	WIRE SIZE AWG	INSULATION COLOR	TERMINAL ID MIN	MWID	LENGTH "L" MAX	"H" ±.010/0.25
	192020062	A-945	192020008	A-945T	22-18	RED	.069/1.75	.147/3.74	1.070/27.18	1.522/38.67
	192020018	B-931	192020022	B-931T	16-14	BLUE	.095/2.41	.185/4.70	1.070/27.18	1.524/38.71
	192020037	C-946	192020042	C-946T	12-10	YELLOW	.139/3.53	.261/6.63	1.150/29.21	1.561/39.65



- NOTES:
1. TERMINAL MATERIAL: COPPER
 2. TERMINAL FINISH: TIN
 3. INSULATION MATERIAL: NYLON 6/6
 4. MWID = MAXIMUM WIRE INSULATION DIAMETER
 4. ASSEMBLY IS ROHS COMPLIANT.

INITIAL RELEASE EC NO: ETC2007-0242 DRW: EHILE 2006/12/14 CHKD: JMACNEIL 2006/12/14 APPR: JMACNEIL 2006/12/14 A	DESCRIPTION	QUALITY SYMBOLS ▽=0 C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY EHILE	DATE 2006/12/13	TITLE BUTT CONNECTOR, SEAMED, NYLAKRIMP MOLEX INCORPORATED	
			4 PLACES	±----	±----	CHECKED BY JMACNEIL	DATE 2006/12/13		
			3 PLACES	±----	±----	APPROVED BY JMACNEIL	DATE 2006/12/13		
			2 PLACES	±----	±----	MATERIAL NO. SEE CHART			
1 PLACE	±----	±----	ANGULAR ±---°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				