

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0398700603

Status:


Obsolete

Description:

5.00mm (.197") Pitch Beau™ Eurostyle™ Right Angle PCB Header, Open Ends, Stackable, 3 Circuits

Replacement Part Number:

39522-0003



Series

image - Reference only

Documents:

[Drawing \(PDF\)](#)

Agency Certification

CSA	LR25562
UL	E48521

General

Product Family	Terminal Blocks
Series	39870
Application	Wire-to-Board
Comments	Gold plating and green housing available
Component Type	PCB Header
Product Name	Eurostyle™ Pluggable
Replacement Part Number	39522-0003
Type	Euro Block

Physical

Circuits (Loaded)	3
Color - Resin	Black
Entry Angle	N/A
Flammability	94V-0
Lock to Mating Part	None
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.30mm (.130")
PCB Retention	N/A
Panel Mount	No
Pitch - Mating Interface	5.00mm (.197")
Pitch - Termination Interface	5.00mm (.197")
Plating min - Mating	3.810µm (150µ")
Plating min - Termination	3.810µm (150µ")
Polarized to Mating Part	Yes
Shrouded	Open Ends
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	15A
Voltage - Maximum	300V

Solder Process Data

Lead-free Process Capability	Wave Capable (TH only)
------------------------------	------------------------

Material Info

Old Part Number	871803
-----------------	--------

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39870Series

Mates With

39870 Plugs

Reference - Drawing Numbers

Sales Drawing

SD-39870-007

This document was generated on 05/17/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION