

10 9 8 7 6 5 4 3 2 1

NOTES: 1. MATERIAL:

HOUSING: POLYESTER, G.F. (UL 94V-0), COLOUR - BLACK.

TERMINAL: PHOSPHOR BRONZE.

2. TERMINAL PLATING:

90635-***1 : CONTACT AREA: GOLD FLASH (0.1um)/ 4uin MIN.

I.D. AREA: TIN (1um)/ 39uin MIN. OVER

NICKEL (1um)/ 39uin MIN.

90635-***2 :CONTACT AREA: GOLD (0.76um)/ 30uin MIN

I.D. AREA: TIN (1um)/ 39uin MIN. OVER

NICKEL (1um)/ 39uin MIN.

90635-***3 :CONTACT AREA: GOLD (0.38um)/ 15uin MIN

I.D. AREA: TIN (1um)/ 39uin MIN. OVER

NICKEL (1um)/ 39uin MIN.

90635-***4 :CONTACT AREA: GOLD (0.51um)/ 20uin MIN

I.D. AREA: TIN (1um)/ 39uin MIN. OVER

NICKEL (1um)/ 39uin MIN.. 20 & 50 CIRCUIT SIZES ONLY

3. FOR USE WITH No. 26 & 28 AWG STRANDED WIRE (7 CONDUCTORS)
AND No. 28 SOLID WIRE 1.14/(.045) DIA. MAX. INSULATION RIBBON
CABLE WITH 1.27/(.050) CENTERS.

4. MATING STRAIN RELIEF: MOLEX No. 90170.


5. DIMENSION "E" IS TOTAL HEIGHT AFTER ASSEMBLED WITH CABLE.
E= 10.5/(.413) REF. WITHOUT STRAIN RELIEF.

E= (15.2)/.598 MAX. WITH STRAIN RELIEF No. 90170.

(14.5)/.571 REF. WHEN COMPRESSED .

6. FOR PRODUCT SPECIFICATION, SEE PS 99020-0015.

64	90635-64*	(78.74) 3.100	(82.54) 3.250	(83.31) 3.280	(85.88) 3.381
60	90635-60*	(73.66) 2.900	(77.46) 3.050	(78.23) 3.080	(80.80) 3.181
50	90635-50*	(60.96) 2.400	(64.76) 2.55	(65.53) 2.580	(68.10) 2.681
40	90635-40*	(48.26) 1.900	(52.06) 2.050	(52.83) 2.080	(55.40) 2.181
34	90635-34*	(40.64) 1.600	(44.44) 1.750	(45.21) 1.780	(47.78) 1.881
30	90635-30*	(35.56) 1.400	(39.36) 1.550	(40.13) 1.580	(42.70) 1.681
26	90635-26*	(30.48) 1.200	(34.28) 1.350	(35.05) 1.380	(37.62) 1.481
24	90635-24*	(27.94) 1.100	(31.74) 1.250	(32.51) 1.280	(35.08) 1.381
20	90635-20*	(22.86) .900	(26.66) 1.050	(27.43) 1.080	(30.00) 1.181
16	90635-16*	(17.78) .700	(21.58) .850	(22.35) .880	(24.92) .981
14	90635-14*	(15.24) .600	(19.04) .750	(19.81) .780	(22.38) .881
10	90635-10*	(10.16) .400	(13.96) .550	(14.73) .580	(17.30) .681
NO. OF CKT.	ENG. NO.	A	B	C	D REF.



REMOVED POLARIZATION EC NO: E2007-0495 DRWN:DBYRNES 2006/12/06 CHKD: 2006/12/07 APPR:EOMAHONY 2006/12/07	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY POB	DATE 1990/09/25	TITLE QIK FLECS SINGLE BEAM FEMALE ASSEMBLY				
			4 PLACES	± ---	± ---	CHECKED BY JDENNEHY	DATE 2005/08/10					
			3 PLACES	± ---	± ---	APPROVED BY JDENNEHY	DATE 2005/08/10					
			2 PLACES	± ---	± ---	MATERIAL NO.		DOCUMENT NO. SDA-90635		SHEET NO. 1 OF 3		
			1 PLACE	± ---	± ---							
			ANGULAR ± ---°			SEE CHART						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9 8 7 6 5 4 3 2 1

HOUSING: POLYESTER, G.F. (UL 94V-0), COLOUR - BLACK.
TERMINAL: PHOSPHOR BRONZE.

90635-***1 : CONTACT AREA: GOLD FLASH (0.1um)/ 4uin MIN.

I.D. AREA: TIN (1um)/ 39uin MIN. OVER
NICKEL (1um)/ 39uin MIN.

90635-***2 :CONTACT AREA: GOLD (0.76um)/ 30uin MIN
I.D. AREA: TIN (1um)/ 39uin MIN. OVER
NICKEL (1um)/ 39uin MIN.

90635-***3 :CONTACT AREA: GOLD (0.38um)/ 15uin MIN
I.D. AREA: TIN (1um)/ 39uin MIN. OVER
NICKEL (1um)/ 39uin MIN.

90635-***4 :CONTACT AREA: GOLD (0.5lum)/ 20uin MIN
I.D. AREA: TIN (lum)/ 39uin MIN. OVER
NICKEL (lum)/ 39uin MIN.

20 & 50 CIRCUIT SIZES ONLY .

3. FOR USE WITH No. 26 & 28 AWG STRANDED WIRE (7 CONDUCTORS) AND No. 28 SOLID WIRE 1.14/(.045) DIA. MAX. INSULATION RIBBON CABLE WITH 1.27/(.050) CENTERS.

4. MATING STRAIN RELIEF: MOLEX No. 90170.

5. DIMENSION "E" IS TOTAL HEIGHT AFTER ASSEMBLED WITH CABLE.
E = 10.5/(.413) REF. WITHOUT STRAIN RELIEF.

E= (15.2)/.598 MAX. WITH STRAIN RELIEF No. 90170.

(14.5)/.571 REF. WHEN COMPRESSED .

6. FOR PRODUCT SPECIFICATION, SEE PS 99020-0015.

REV	DESCRIPTION	DATE
1	REMOVED OPTION EC NO: E2007-0495 DRAWN: DBYRNES CHKD: APPR: EOMAHONY	2006/12/06 2006/12/07 2006/12/07

QUALITY SYMBOLS	
	=0
	=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---
ANGULAR ± ---°		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE

MM/IN	
DRAWN BY	DATE
POB	1990/09/25
CHECKED BY	DATE
JDENNEHY	2005/08/10
APPROVED BY	DATE
JDENNEHY	2005/08/10

MATERIAL NO.	SEE CHART
--------------	-----------

SCALE

E	DESIGN UNITS
---	--------------

METRIC	THIRD ANGLE PROJECTION
--------	---------------------------

QIK FLECS SINGLE BEAM
FEMALE ASSEMBLY,
PRE-LOADED





MOLEX INCORPORATED

DOCUMENT NO.
SDA-90635

SHEET NO.
2 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



FEMALE ASSEMBLY.
PRE-LOADED.
90635-***

WITH POLARISATION =1 OR 9—

CIRCUIT SIZE

PLATING OPTION