



SL-156

TE Internal #: 2-640251-4
Housing, Receptacle, Wire-to-Board, 24 Position, 3.96 mm [.156 in]
Centerline, Crimp, 1 Row, Natural, Wire & Cable, Power & Signal,
SL-156

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >
Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **24**
Centerline (Pitch): **3.96 mm [.156 in]**

[All Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156 \(27\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	24
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

--	--



Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Socket
Contact Current Rating (Max)	6.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Alignment	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon - GF
Housing Entry Configuration	Left End Open
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Height	6.35 mm
	3.746 in
Wire Size	30 – 18 AWG

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Flammability Rating	UL 94V-0

Packaging Features

--	--



Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2479636-1
EXTRACTION TOOL



TE Part # 2-640388-4
24P MTA156 HDR ASSY RN STR F/L



TE Part # 2-640551-4
24P MTA156 COVER



TE Part # 5-641209-4
24P MTA156 HDR ASSY FL ST LF



TE Part # 2-643071-4
24P MTA156 FD-THRU COVER

TE Part # 2-640385-4
24P MTA156 HDR ASSY SQ R/A

TE Part # 2-640383-4
24P MTA156 HDR ASSY STR SQ SN

TE Part # 2-640389-4
24P MTA156 HDR ASSY SQ R/A F/L

TE Part # 2-644752-4
24P MTA156 HDR ASSY SQ STR F/L

TE Part # 2-643067-4
24P MTA156 MOLDED COVER

TE Part # 2-640445-4
24P MTA156 HDR ASSY FL/STR SN

TE Part # 2-641119-4
24P MTA156 HDR ASSY FL/ST 15AU

TE Part # CAT-103156-WBHSN
Receptacle Housing: Wire-to-Board,
no Mating Alignment, SL 156

Also in the Series | SL-156

Connector Contacts(23)

Connector Hardware(4)

Power Contacts(13)

Rectangular Connector Housings(10)

Rectangular Power Connectors(10)

Standard Rectangular Connectors(10)

Wire-to-Board Connector Assemblies
& Housings(140)

Customers Also Bought



TE Part #60773-2
SPADE TERMINAL 18-14 AWG TPBR

TE Part #2-382811-1
SHUNT, ECON, PHBR SN, BLACK

TE Part #2-36161-2
TERM, PIDG, R, 12-10, #10, T&R

TE Part #640255-1
KEYING PIN .045 SQ PST CONN

TE Part #794954-6
6P RCPT VAL-U-LOK V2

TE Part #282847-4
TERMI-BLOK PCB MOUNT 35 4P.5

TE Part #1-66100-9
III+ SKT, 18-16, TIN, STRIP

TE Part #CAT-103156-WBHSN
Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156

TE Part #640254-1
KEYING PLUG .045 SQ PST CONN

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-640251-4_AL_c-2-640251-4-al.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-640251-4_AL_c-2-640251-4-al.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-640251-4_AL_c-2-640251-4-al.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals



UL Report

English