7-353293-0 ✔ ACTIVE


AMP Mini CT

TE Internal #: 7-353293-0

Connector Assembly, Receptacle, Wire-to-Board, 20 Position, 1.5 mm [.06 in] Centerline, Insulation Displacement (IDC), 1 Row, Blue, AMP Mini CT

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **20**

Centerline (Pitch): **1.5 mm [.06 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	20
Number of Rows	1

Body Features

Primary Product Color	Blue

Contact Features

Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Mating Retention Type	Lock
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	1.5 mm[.06 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 7-292231-0
1.5 MINI CT SGL V SMT W/O BOSS



TE Part # 7-292207-0
MINI CT SGL DIP V 20P BLUE



TE Part # 2-292231-0
1.5 MINI CT SGL V SMT W/O BOSS



TE Part # 7-292230-0
1.5 MINI CT SGL V SMT W/BOSS 2



TE Part # 7-292228-0
1.5 MINI CT SGL H SMT W/O BOSS



TE Part # 2-292227-0
1.5 MINI CT SGL H SMT W BOSS 2



TE Part # 2-292207-0
MINI CT SGL DIP V 20P NAT



TE Part # 2-292215-0
MINI CT SGL RELAY 20P NAT



TE Part # 937317-1
MIMI CT PISTOL TOOL



TE Part # CAT-AM7053-H342
MINI COMMON TERMINATION HEADERS




TE Part # 2-292230-0
1.5 MINI CT SGL V SMT W/BOSS 2



TE Part # 9-353294-0
AMP MINI D/R HDR HSG 40P BLUE



TE Part # 7-292215-0
MINI CT SGL RELAY 20P BLUE



TE Part # 9-292262-0
DBL ROW (H) DIP TYPE WITH BOAR



TE Part # 7-292272-0
S/R POST HDR ASSY V DIP AU-PL. 20P BLUE




TE Part # 7-292227-0
1.5 MINI CT SGL H SMT W BOSS 2


Also in the Series | AMP Mini CT



Connector Contacts(4)




Connector Hardware(10)



PCB Headers & Receptacles(332)



Wire-to-Board Connector Assemblies & Housings(172)



Wire-to-Board Headers & Receptacles (332)

Customers Also Bought



TE Part #3-292215-8
MINI CT SGL RELAY 18P BLACK



TE Part #2-292156-3
CT RELAY HDR ASSY FREE HANGING




TE Part #2-292215-8
MINI CT SGL RELAY 8P BLACK



TE Part #2-292215-6
MINI CT SGL RELAY 6P BLACK



TE Part #6-179228-3
CT CRIMP-2 REC HSG 3P BLACK



TE Part #3-292234-0
1.5 MINI CT DC DRAWER PLUG ASS



TE Part #3-292215-0
MINI CT SGL RELAY 10P BLACK



TE Part #3-292215-2
MINI CT SGL RELAY 12P BLACK



TE Part #292274-1
1.5 MINI CT CRIMP CONTACT

TE Part #9-292155-4
SGL HDR PANEL MOUNT ASSY

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_7-353293-0_K.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-353293-0_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-353293-0_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

Japanese

AMP MINI CCOMMON TERMINATION (CT), CONNECTOR, 1.5mm PITCH, M/T TYPE, LEAD FREE VERSION

Japanese

Product Specification

English

Instruction Sheets

AIR MINI PRESS FOR AMP MINI CT CONNECTOR

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet for Mini CT DC Drawer Connector SF Type

Japanese

Instruction Sheet (non U.S.)

English

1.5mm Pitch Mini CT DC Drawer Connector SF Type

Japanese

Instruction Sheet (non U.S.)

Japanese

1.5mm Pitch Mini CT Hybrid Drawer Connector SF Type

Japanese

Instruction Sheet (non U.S.)

Japanese

1.5mm Pitch Mini CT Hybrid Drawer Connector Slim Type

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

UL

English