



AMP CT

TE Internal #: 2-173977-4

Connector Assembly, Receptacle, Wire-to-Board, 4 Position, 2 mm [.079 in] Centerline, Insulation Displacement (IDC), 1 Row, Blue, Wire & Cable, AMP CT

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **2 mm [.079 in]**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

--	--



Contact Current Rating (Max)	2 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2 mm[.079 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 292254-4 CT RELAY HDR ASSY 4P NAT	 TE Part # 2-292251-4 CT P/HDR BOX V 4P POL BLUE	 TE Part # 2-292170-4 CT P/HDR ASSY 4P V W/O KINK T	 TE Part # 58372-1 HEAD (IDC) 2MM C.T. W/O TL
 TE Part # 2-292156-4 CT RELAY HDR ASSY FREE HANGING	 TE Part # CAT-3983178-PHBXVD CT 2mm Post Header Asmbly: Box V DIP	 TE Part # CAT-3984552-BHHSV CT Box Header SMT: Vert, Shrouded	 TE Part # 2-292164-4 CT P/HDR BOX H ASSY 4P T/P BLU
 TE Part # 2-292165-4 CT P/HDR BOX V 4P T/P BLUE	 TE Part # 5-292271-4 MT REC ASSY AU-PL. 4P BLUE	 TE Part # 2-173983-4 AMP CT MT AMP-IN HDR-H YEL 4P	 TE Part # CAT-3980407-RHRRRA CT 2mm Header Assembly: Right Angle
 TE Part # CAT-AM7017-H342 AMP COMMON TERMINATION HEADERS	 TE Part # 2-292145-4 CT P/HDR ASSY V 4P W/O KINK BL	 TE Part # 2-292254-4 CT RELAY HDR ASSY 4P BLUE	 TE Part # 2-292157-4 CT RELAY W/COMMONING BAR 4P NA



TE Part # 2-292161-4
CT P/HDR ASSY V 4P W/KINK BLUE



TE Part # 2-173985-4
AMP CT MT AMP-IN HDR-V BLU 4P




TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME


Also in the Series | AMP CT



Connector Contacts(8)



Connector Hardware(46)




PCB Headers & Receptacles(756)



Rectangular Power Connectors(749)



Wire-to-Board Connector Assemblies & Housings(255)




Wire-to-Board Headers & Receptacles (756)


Customers Also Bought



TE Part #3-353293-5
1.5MM CT MT REC ASSY 15P BLACK




TE Part #3-292216-2
MINI CT D/R RELAY 32P V NAT



TE Part #5-160432-4
250 FASTON REC 20-16 AWG TPBR



TE Part #2-353293-8
1.5MM CT MT REC ASS'Y 8P BLACK




TE Part #3-353293-4
1.5MM CT MT REC ASSY 14P BLACK



TE Part #1SNG601180R0000
EP-SG-NPT1-BL-B



TE Part #1SNG609031R0000
ENBR-WG-NPT1-BL-A



TE Part #170262-2
EIS CONTACT



TE Part #3-353293-1
1.5MM CT MT REC ASSY 11P BLACK



TE Part #173977-3
CT CONN MT REC ASSY 3P

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_2-173977-4_M.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-173977-4_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-173977-4_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

MINI PRESS CT CONNECTOR (WAS IS-553J)

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

CSA Certificate

English

CSA Certificate

English