




MTA 156

TE Internal #: 3-640602-5

Connector Assembly, Receptacle, Insulation Displacement (IDC),
Wire-to-Board, Tin (Sn), MTA 156, Rectangular Wire & Cable
Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **Without**
Mating Retention: **With**
Mating Retention Type: **Locking Ramp**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Power Positions	5
Number of Positions	5
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Cable Exit Angle	90°
------------------	-----



Primary Product Color	White
Contact Features	
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	30 µm[.762 µin]
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
Wire Contact Termination Area Plating Thickness	2.03 – 5.08 µm[80 – 200 µin]
Contact Type	Receptacle
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
Strain Relief	With
Panel Mount Feature	Without
Contact Retention Type Within Housing	Locking Lance
Mating Alignment	Without
Mating Retention	With
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Nylon
Wire & Cable IDC Installation Type	Feed Through
Centerline (Pitch)	3.96 mm[.156 in]
Dimensions	
Compatible Insulation Diameter Range	2.41 mm[.095 in]
Connector Height	9.78 mm[.385 in]
Wire Size	24 AWG



Connector Length19.81 mm[.78 in]

Usage Conditions

Operating Temperature Range-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit ApplicationPower & Signal

Industry Standards

Compatible With Agency/Standards ProductsCSA, UL

UL RatingRecognized

Compatible With Approved Standards ProductsUL E28476

CSA RatingCertified, LR 7189

Glow Wire RatingStandard Part - Not Glow Wire

UL Flammability RatingUL 94V-2

Packaging Features

Packaging Quantity250

Packaging MethodBag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EUCompliant

EU ELV Directive 2000/53/ECCompliant

China RoHS 2 Directive MIIT Order No 32, 2016No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen ContentLow Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process CapabilityNot applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 3-644613-5 05P MTA156 HDR RA PO WO PEG LF	 TE Part # 3-644615-5 05P MTA156 POL HDR ASSY LF	 TE Part # 643495-3 05P MTA156 HDR ASSY W/O#2	 TE Part # 640389-5 05P MTA156 HDR ASSY SQ R/A F/L
 TE Part # 640385-5 05P MTA156 HDR ASSY SQ R/A	 TE Part # 643067-5 05P MTA156 MOLDED COVER	 TE Part # 643495-1 05P MTA156 HDR ASSY W/O#4	 TE Part # 640383-5 05P MTA156 HDR ASSY STR SQ SN
 TE Part # 640384-5 05P MTA156 HDR ASSY STR RND SN	 TE Part # 640445-5 05P MTA156 HDR ASSY FL/STR SN	 TE Part # 640388-5 05P MTA156 HDR ASSY RN STR F/L	 TE Part # 644749-5 05P MTA156 HDR ASSY STR SQ SN
 TE Part # 643071-5 05P MTA156 FD-THRU COVER	 TE Part # 58443-1 MTA 156 CRIMP HEAD PRODUCTION FEED THRU	 TE Part # 644752-5 05P MTA156 HDR ASSY SQ STR F/L	 TE Part # 640643-5 05P MTA156 COVER F/T




TE Part # 59804-1
MAINTENANCE TOOL



TE Part # 644751-5
05P MTA156 HDR ASSY R/A



TE Part # 3-644617-5
05P MTA156 HDR ASY PO RA FB LF



TE Part # 2-647125-5
05P MTA156 SHRD HDR ASSY LF

Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)



Connector Hardware(2)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(677)



Power Contacts(3)




Rectangular Power Connectors(1178)




Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #3-640600-5
05P MTA156 CONN ASSY 20AWG LF




TE Part #63306-2
250 FASTON REC 18-14 AWG TPBR




TE Part #YDTS26W13-35SNV001
PLUG ASSY



TE Part #CAT-R21-T319
Single Wall RT 1145: Heat Shrink Tubing



TE Part #207345-1
CABLE CLAMP KIT,SZ 3



TE Part #207470-1
CABLE CLAMP KIT,SZ 2



TE Part #3-640601-5
05P MTA156 CONN ASSY 22AWG LF



TE Part #206038-2
CPC RECPT ASSEMBLY SIZE 17-28



Documents

Product Drawings

05P MTA156 CONN ASSY 24AWG LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-640602-5_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-640602-5_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-640602-5_V.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_3-640602-5_Z.3d_igs.zip

English

Customer View Model

ENG_CVM_3-640602-5_Z.3d_stp.zip

English

Customer View Model

ENG_CVM_3-640602-5_Z.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)



English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese

[Application Specification](#)

English

[Agency Approvals](#)

[Agency Approval Document](#)

English