



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **8, 16**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Breakaway
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Board-to-Board Configuration	Parallel
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	8, 16
Number of Rows	2

Body Features

Primary Product Color	Green
-----------------------	-------

Contact Features

Contact Mating Area Plating Material Thickness	.1 µm[3.94 µin]
Mating Square Post Dimension	.64 mm[.025 in]
Contact Shape & Form	Square
Contact Mating Area Length	5 mm[.197 in]
Contact Base Material	Copper Tin



Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	5 A

Termination Features

Termination Post & Tail Length	3 mm[.118 in]
Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Housing Material	PBT GF, PBTP GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Stack Height	27.3 mm[1.074 in]
PCB Thickness (Recommended)	1.4 mm[.055 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024
(241)
Candidate List Declared Against: JAN 2023
(233)
Does not contain REACH SVHC




Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | AMPMODU Headers

 Automotive Headers(1)	 Board-to-Board Headers & Receptacles(1576)	 Connector Contacts(47)	 Connector Hardware(1)
 PCB Headers & Receptacles(1621)	 Rectangular Power Connectors(43)	 Wire-to-Board Connector Assemblies & Housings(5)	 Wire-to-Board Headers & Receptacles (114)

Customers Also Bought







TE Part #9-2176092-4
RP 2A 0.25W 7K68 0.1% 25PPM 1K RL



TE Part #1622442-1
LR1 1% 33R



TE Part #281739-8
HEADER HE14 STRAIGHT 2X8 P



TE Part #1982295-1
ELCON MINI 2P RA HEADER, W /CODING




TE Part #1-770966-0
02P MINI UMNL R/A HDR ASSY SN




TE Part #794894-1
02P MINI UMNL PLUGS WIRE HOLES



TE Part #1393230-9
RP3SL012



TE Part #170267-1
250 FASTON,PCB TAB,TCBR



TE Part #2176481-1
RA73F 1J 5K9 0.1% 5K RL



TE Part #770968-2
04P MINI UMNL R/A HDR ASSY AU

Documents

CAD Files

Customer View Model

ENG_CVM_829822-8_O1.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_829822-8_O1.3d_igs.zip

English

Customer View Model

ENG_CVM_829822-8_O1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU Interconnetion System

AMPMODU Interconnetion System

English

