

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		E2	REV PER ECO 11-015338	26JUL11	JR	SM

D

C

B




A

D


C

B

A



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [.062] THICK P.C. BOARD



- 1 MATERIAL
HOUSING: THERMOPLASTIC POLYESTER, GLASS FILLED, UL94V-O.
POST: COPPER ALLOY
- 2 FINISH
HOUSING: NATURAL
POST: BRIGHT TIN-LEAD (93/7) PLATE, 0.00380-0.00880 [.000150-.000350] THK OVER NICKEL UNDERPLATE, 0.00130 [.000050] MIN THK.
- 3 UL MARKING MAY NOT APPEAR ON THE 2 OR 3 POSITION SIZES.
CSA MARKING MAY NOT APPEAR ON THE 2 POSITION SIZE.
- 4 POST SOLDER TAILS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-2.
- 5 POST WITHSTANDS 13.34N [3 LB] MIN AXIAL FORCE IN EITHER DIRECTION WITHOUT DISLODGING.
- 6 APPLIES AT -A-
- 7 APPLIES WHEN THE HEADER IS STRAIGHT.
- 8 PLASTIC PROJECTIONS PERMITTED IN THIS ZONE.
- 9 COORDINATE DIMENSIONS APPLIES FROM THE CENTER OF THE ACTUAL FEATURE.
- 10 SOLDER SIDE OF BOARD IS SHOWN.
- 11 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 12 ALL POSITION SIZES HAVE THE BACKWALL NOTCHED ON BOTH ENDS AS SHOWN. THE 2 THRU 5 POSITION SIZES HAVE SOLID BACKWALLS. POSITION SIZES 6 AND ABOVE HAVE AN INTERRUPTED BACKWALL AT VARIOUS LOCATIONS (SEE TABLE FOR INTERRUPTION(S) LOCATIONS).
- 13 EDGE OF POLARIZING LOCK WALL TO BE IN LINE WITH CENTERLINE OF ADJACENT POST WITHIN ±0.13 [.005]
- 14 FINISH
HOUSING: NATURAL
POST: MATTE TIN PLATE 0.000150 MIN THICK OVER NICKEL,
- 15 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

15 SUPERSEDED

15 SUPERSEDED

15 SUPERSEDED

15 SUPERSEDED

14	4&5, 7&8, 11&12, 14&15	71.20 [2.803]	18	4-644613-8
	4&5, 7&8, 10&11, 13&14	67.23 [2.647]	17	4-644613-7
14	4&5, 8&9, 12&13	63.27 [2.491]	16	4-644613-6
	4&5, 8&9, 11&12	59.31 [2.335]	15	4-644613-5
14	4&5 7&8, 10&11	55.35 [2.179]	14	4-644613-4
	4&5 7&8, 10&11	51.38 [2.023]	13	4-644613-3
14	4&5, 8&9	47.42 [1.867]	12	4-644613-2
	4&5, 7&8	43.46 [1.711]	11	4-644613-1
14	3&4, 7&8	39.50 [1.555]	10	4-644613-0
	3&4, 6&7	35.53 [1.399]	9	3-644613-9
14	4&5	31.57 [1.243]	8	3-644613-8
	4&5	27.61 [1.087]	7	3-644613-7
14	3&4	23.65 [.931]	6	3-644613-6
	NONE	19.69 [.775]	5	3-644613-5
14	NONE	15.72 [.619]	4	3-644613-4
	NONE	11.76 [.463]	3	3-644613-3
14	NONE	7.80 [.307]	2	3-644613-2
	4&5, 7&8, 11&12, 14&15	71.20 [2.803]	18	1-644613-8
14	4&5, 7&8, 10&11, 13&14	67.23 [2.647]	17	1-644613-7
	4&5, 8&9, 12&13	63.27 [2.491]	16	1-644613-6
14	4&5, 8&9, 11&12	59.31 [2.335]	15	1-644613-5
	4&5 7&8, 10&11	55.35 [2.179]	14	1-644613-4
14	4&5 7&8, 10&11	51.38 [2.023]	13	1-644613-3
	4&5, 8&9	47.42 [1.867]	12	1-644613-2
14	4&5, 7&8	43.46 [1.711]	11	1-644613-1
	3&4, 7&8	39.50 [1.555]	10	1-644613-0
14	3&4, 6&7	35.53 [1.399]	9	644613-9
	4&5	31.57 [1.243]	8	644613-8
14	4&5	27.61 [1.087]	7	644613-7
	3&4	23.65 [.931]	6	644613-6
14	NONE	19.69 [.775]	5	644613-5
	NONE	15.72 [.619]	4	644613-4
14	NONE	11.76 [.463]	3	644613-3
	NONE	7.80 [.307]	2	644613-2
FINISH	BACKWALL INTERRUPTION(S) BETWEEN POST	L	NO. OF POSITIONS	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SMITH 2-12-93	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.SWING 2-12-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.CLARK 15-12-93	NAME MTA-156 HEADER ASSEMBLY, POLARIZED LOCK, RIGHT ANGLE FRONT BEND, .045 SQUARE POST, TIN-LEAD PLATED, WITHOUT RETENTION PEGS	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	SIZE A1	
MATERIAL		APPLICATION SPEC	CAGE CODE 00779	
FINISH		WEIGHT	DRAWING NO 644613	
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	
		REV E2		