



Part Number : [731716611](#)
Product Description : 75 Ohms, BNC Jack, Right-Angle, Bulkhead, PCB Through Hole, 12 GHz, with Low-Profile Jam Nut and Washer, 2.01mm Peg Length, Tray
Series Number : 73171
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings
[731716611_sd.pdf](#)

3D Models and Design Files
[731716611_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	75 Ohms, BNC Jack, Right-Angle, Bulkhead, PCB Through Hole, 12 GHz, with Low-Profile Jam Nut and Washer, 2.01mm Peg Length, Tray
Product Name	BNC
Style	PCB
Type	Miniature
UPC	889056242509

Electrical

Frequency	12 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	15.352/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	1.60mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----