



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 13100 – 20800 CMA

Stud Size: 5/8, M16

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	5/8, M16
Sealable	No

Wire Insulation Support Retention Type	Non-Insulation Support
--	------------------------

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	9.546 g
----------------	---------

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	13100 – 20800 CMA
Stud Diameter	16.66 mm[.656 in]
Tongue Thickness	1.22 mm[.05 in]
Product Length	49.91 mm[1.96 in]
Barrel Inside Diameter	4.37 mm[.172 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part





numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1901002-2 INDENTER, SOLISTRAND	 TE Part # 48126 HYP8 SOLIS 8AWG NEST	 TE Part # 1901001-1 NEST #8	 TE Part # 48355 HYP8 SOLIS 8AWG INDENTER
 TE Part # 49956 PNEUMATIC SOLIS STRATO 8 HEAD	 TE Part # 69216 HYP8/10 SOLIS 8AWG DIE SET	 TE Part # 69355 HHHT SOLIS SOLIS FLAG STRATO 8 ASSY	 TE Part # 1490413-1 HYP10 SOLIS 8AWG NEST
 TE Part # 1490414-1 HYP10 SOLIS 8AWG INDENTER	 TE Part # 69339 HHHT SOLIS SOLIS FLAG STRATO 8 ASSY		

Customers Also Bought

 TE Part #1-532447-2 HDI PIN ASSY 3 ROW 225 POS	 TE Part #34945 SPLICE,PG BUTT 12-10	 TE Part #208480-1 CMC PLUG ASSEMBLY,SZ 28	 TE Part #35669 TERMINAL,SOLIS R 4 5/8
---	--	--	--



Documents

Product Drawings

[TERMINAL,SOLIS R 8 5/8](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_35665_P.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_35665_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_35665_P.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_35665_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_35665_D.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_35665_D.2d_dxf.zip](#)

English

[3D PDF](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English

UL Report

English