

锂电池 UN38.3 试验概要
Lithium Battery Test Summary

报告编号: LA2024B1265001UNZY

单位信息 Company Information					
委托单位 Consignor	宁波奥马电器科技有限公司 / Ningbo Auma Electric Technology Co., Ltd. 浙江省余姚市泗门镇姚北大道 20 号 No.20th Yaobei Road, Simen Town, Yuyao City, Zhejiang province China 电话/Tel: +86 574 62861007 邮箱/Mail: admin@nbauma.cn				
生产单位 Manufacturer	四川创科慧科技有限公司 / Sichuan Chuangkehui Technology Co., Ltd 四川省资阳市乐至县天童大道 1503 号 A2 栋、A4 栋 / Building A2 & A4, No.1503, Tiantong Avenue, Lezhi County, Ziyang City, Sichuan Province, China. 电话/Tel: 17722413350 邮箱/Mail: liaojin@ckh-battery.com 网址/Website: www.szckhkj.com				
测试单位 Test Lab	深圳市莱恩瑞斯科技有限公司 Shenzhen Lionaces Technology Co., Ltd. 深圳市宝安区福海街道和平社区永和路骏丰工业区 B6 栋 301 301, Building B6, Junfeng Industrial Zone, Yonghe Road, Heping Community, Fuhai Street, Baoan, Shenzhen, Guangdong, China 电话/Tel: 0755-28280690 邮箱/Mail: service@lionaces.com 网址/Website: www.lionaces.com				
电池信息 Battery Information					
名称 Name	锂离子电池组 Li-ion Battery Pack	电池/电芯类别 Battery/Cell Classification		单电芯锂离子电池 Single Cell Li-ion Battery	
型号 Type	18650	商标 Trademark		/	
额定电压 Normal Voltage	3.7V	额定容量 Rated Capacity		2600mAh	
额定能量 Watt-hour rating	9.62Wh	外观/Appearance		蓝色近圆柱体 Approximate Blue Cylinder	
质量/Mass	45.85g	锂含量/Li Content		不适用 N/A	
测试信息 Test Information					
测试报告编号 Test Report Number	LA2024B1265001U		测试报告签发日期 Date of Test Report	2024-09-20	
测试标准 Edition of UN Manual of Tests and Criteria Used	联合国《试验和标准手册》(第 8 版) 38.3 节 UN "Manual of Tests and Criteria" ST/SG/AC.10/11/Rev.8/Subsection 38.3				
T.1: 高度模拟 Altitude Simulation	通过 Pass	T.2: 温度试验 Thermal Test	通过 Pass	T.3: 振动 Vibration	通过 Pass
T.4: 冲击 Shock	通过 Pass	T.5: 外部短路 External Short Circuit	通过 Pass	T.6: 撞击/挤压 Impact/Crush	通过 Pass
T.7: 过度充电 Overcharge	通过 Pass	T.8: 强制放电 Forced Discharge	通过 Pass	/	
UN38.3.3(f)	不适用 N/A		UN38.3.3(g)	不适用 N/A	
签名 Signatory	[Signature]		签发日期 Issued Date	2024-09-20	
职务 Title	测试工程师				

The results shown in this test report refer only to the sample(s) tested unless otherwise stated and the samples are retained for 30 days only. The document is issued by Lionaces. It cannot be reproduced except in full with our prior written permission. The document is available on request and the brief information for its validation can be assessed and confirmed on the website, <http://www.lionaces.com>