



Part Number : [1202540116](#)

Product Description : Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, PNP, Changeover/IOL, Potentiometer Sensitivity Adjustment, 4-pin M12 Connector, 37mm Housing Length

Series Number : 120254

Status : Active

Product Category : Inductive and Photoelectric Sensors

Engineering Number : LTR-M18PA-PMS-603



Documents & Resources

Specifications

[1202540114-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120254
Description	Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, PNP, Changeover/IOL, Potentiometer Sensitivity Adjustment, 4-pin M12 Connector, 37mm Housing Length
IP Rating	IP67
Operating Principle	Diffuse
Product Name	Contrinex
Type	Photoelectric
UPC	191130068524

Electrical

Output	Changeover/IOL
Polarity	PNP
Switching Frequency	≤ 1500 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	37mm
Material - Housing	ABS
Material - Window	PMMA
Net Weight	99.000/g
Operating Distance	3 - 1200mm
Output	Changeover/IOL
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C
