



Part Number : [1202530456](#)
Product Description : Contrinex Inductive Sensor, 40 x 40mm Housing, 40mm Operating Distance, Non-embeddable, PNP, NO/NC (antivalent), 4-pin M12 Connector, 67mm Housing Length
Series Number : 120253
Status : Active
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AS-63A-C44



Documents & Resources

Specifications
[1202530456-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120253
Description	Contrinex Inductive Sensor, 40 x 40mm Housing, 40mm Operating Distance, Non-embeddable, PNP, NO/NC (antivalent), 4-pin M12 Connector, 67mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130067817

Electrical

Output	NO/NC (antivalent)
Polarity	PNP
Switching Frequency	≤ 100 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	67mm
Material - Housing	PA Glass-filled
Material - Sensing Face	PA Glass-filled
Mounting Style	Non-embeddable
Net Weight	444.000/g
Operating Distance	40mm
Output	NO/NC (antivalent)
Sensor Housing Size	40 x 40mm
Temperature Range - Operating	-25° to +85°C