



Part Number : [2147522022](#)
Product Description : Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Gold (Au) Plating, 2 Circuits, Black
Series Number : 214752
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2147522022_sd.pdf](#)

3D Models and Design Files
[2147522022_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	214752
Description	Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Gold (Au) Plating, 2 Circuits, Black
Application	Power, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Product Name	Micro-Fit 3.0
Type	Discrete Wire Assembly
UPC	193264585908

Electrical

Current - Maximum per Contact	8.5A
Voltage - Maximum	300V AC/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	8.208/g

Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	Discrete Wire, UL 10002
Wire Insulation Diameter	1.85mm max.
Wire Size (AWG)	18

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Single Row Receptacle Housings	<u>43645</u>