



Part Number : [451460210](#)
Product Description : Squba-to-Squba Off-the-Shelf (OTS) Plug Cable Assembly, Single Row, 1.0m, 2 Circuits, Black
Series Number : 45146
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[451460210_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	45146
Description	Squba-to-Squba Off-the-Shelf (OTS) Plug Cable Assembly, Single Row, 1.0m, 2 Circuits, Black
Application	Power, Signal, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Squba-to-Squba
Product Name	Squba
Type	Discrete Wire Assembly, Sealed Assembly
UPC	191128910156

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	125V

Physical

Cable Length	1.0m
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	15.024/g
Number of Rows	1
Overmolded	No

Packaging Type	Bag
Pitch - Mating Interface	1.80mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba 1.8 Sealed Single Row Receptacle Assemblies	<u>204220</u>