




Part Number : [2125700200](#)
Product Description : 824MHz-2170MHz Side-Fed Cellular Flexible Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 212570
Status : Active
Product Category : Antennas



Documents & Resources

Drawings
[2125700200_sd.pdf](#)
[2125700100-001.pdf](#)

3D Models and Design Files
[2125700200_stp.zip](#)

Specifications
[2125700100-000.pdf](#)
[2125700100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Antennas
Series	212570
Description	824MHz-2170MHz Side-Fed Cellular Flexible Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	Side-Fed Cellular Flexible
Protocol	Cellular
Type	Cellular Antenna, Internal
UPC	193264168811

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	824
Band#2 F_End (MHz)	2170
Band#2 F_Start (MHz)	1710
Electrical Connectivity	Cable
Peak Gain (dBi)	-0.45 @ 824 MHz, 1.76 @ 1710 MHz
Return Loss - S11 (dB)	< -5
Total Efficiency	>35% @ 824 MHz, >50% @ 1710 MHz

Physical

Cable Length	200.00mm
Length	40.40mm
Mounting Style	Adhesive

Net Weight	1.048/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	15.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
50 Ohms, MCRF, PCB Vertical Jack Receptacle, SMT, 1.25mm Mounted Height	<u>734120110</u>