



TE Internal #: 1-2016703-0
SMA to N Type Cable Assembly, 1 m [3.28 ft], Black Cable, 50 ohm, PUR Jacket, 19 AWG, 10.2 mm [.4 in] Diameter, SMA Plug End A, N TYPE Plug End B
[View on TE.com >](#)

Cable Assemblies > RF Cable Assemblies



Cable Assembly Type: **SMA to N Type**
Cable Assembly Length: **1 m [3.28 ft]**
Cable Color: **Black**
Impedance: **50 Ω**
Jacket Material: **PUR**

Features

Product Type Features

Cable Assembly Type	SMA to N Type
Cable Assembly (End A)	SMA Plug
Cable Assembly (End B)	N TYPE Plug

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Strain Relief Type	HST
Cable Color	Black
Jacket Material	PUR

Dimensions

Wire Size	19 AWG
Outside Cable Diameter	10.2 mm[.4 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------



Operation/Application

Shielded	Yes
----------	-----

Other

Cable Assembly Length	1 m[3.28 ft]
-----------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2081553-1
ADAPTOR 4.1-9.5 PLUG TO N JACK



TE Part # 2081570-2
2.92MM JACK 2 HOLE FLANGE RECEPTACLE



TE Part # 1059733-1
BSA, OSP Jack-SMA Jack BHD 4584 2244 02



TE Part # 2081562-1
ADAPTER N FEMALE TO N FEMALE





TE Part # 2081934-1
2.92MM JACK PCB EDGE LAUNCH



TE Part # 2081570-1
2.92MM JACK 2 HOLE FLANGE RECEPTACLE



TE Part # 1059731-1
4584 2242 02



TE Part # 1-1337406-0
N Str Jk PS 50Ohm Silver Pltd PSF 1 /4M,



TE Part # 1058117-1
3284 2240 00



TE Part # 225094-1
N SER BHD JACK WEATHERPROOF



TE Part # 2081563-1
ADAPTER N FEMALE TO N FEMALE 4-H FLG-MT



TE Part # 2408014-1
SMA FEMALE ST TO SWITCH



TE Part # 1057290-1
3052 1201 10,N SERIES FM PLUG



TE Part # 1059724-1
4583 2240 02



TE Part # 1057377-1
3082 2240 00,ADAPTER,N TO SMA

Customers Also Bought



TE Part #35492
PG RING 12-10 1/4 STUD



TE Part #2-34148-1
PG R 22-16 COMM 22-18 MIL 8



TE Part #696047-1
TERMINAL PG 12-10, 8



TE Part #2-34146-5
PG R 22-16 COMM 22-18 MIL 10

Documents

Product Drawings
N M TO SMA M,18G,1.0M WITH ARMOR
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-2016703-0_A.2d_dxf.zip

1-2016703-0

SMA to N Type Cable Assembly, 1 m [3.28 ft], Black Cable, 50 ohm, PUR Jacket, 19 AWG, 10.2 mm [.4 in] Diameter, SMA Plug End A, N TYPE Plug End B



English

Customer View Model

[ENG_CVM_CVM_1-2016703-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2016703-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English