




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (2% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought



TE Part #NB20314001
VERSAFIT-3/16-0-SP-SM




TE Part #6635996003
LSTT-R-1.6-0




TE Part #1-1734742-8
.5 FPC VT ZIF Type-A 18 CONT



TE Part #521384-4
ASSY PL R/A RAST5 HEADER 04-A




TE Part #2337992-5
RJ45 JACK MAG. POE 1GB LED 1X1 INV.



TE Part #1-215911-6
16 WAY GREY MK II RECP



TE Part #4-1618391-2
LEV100A6ANH=RELAY,SPST-NO, 48VDC VMT 15



TE Part #7-2176397-5
3502 1K2 1%



TE Part #2-1676481-4
CPF 0603 47R 0.1% 25PPM 1K RL



TE Part #925574-2
RTV SOCKET

Documents

Product Drawings

AMPL REC, HD22, R/A, 15P, THREADED, BLUE

English

CAD Files

Customer View Model

ENG_CVM_CVM_2311586-4_B2.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2311586-4_B2.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2311586-4_B2.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Product Specification

English