




TE Internal #: 4-2271013-0
PCB Mount Header, Right Angle, Board-to-Board, 96 Position, 2.54 mm [.1 in] Centerline, Fully Shrouded, Gold Flash, Through Hole - Solder, Signal
[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Right Angle**
Connector System: **Board-to-Board**
Number of Positions: **96**
Number of Rows: **3**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Board-to-Board Configuration	Perpendicular
PCB Mount Orientation	Right Angle
Number of Positions	96
Number of Rows	3

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.076 µm[2.99 µin]
PCB Contact Termination Area Plating Material Thickness	2.54 µm[100 µin]
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold Flash
Contact Type	Pin
Contact Current Rating (Max)	2 A

Termination Features

Rectangular Termination Post & Tail Thickness	2 mm
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	30
Packaging Method	Tray



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 8-2271014-0
CELLO,REC,96P,TH,V,FG,DIP4.57,-



TE Part # 4-2834379-0
CELLO,REC,96P,TH,RA,FG,DIP3.0,



TE Part # 4-2271014-0
CELLO,REC,96P,TH,V,FG,DIP3.0,-



TE Part # 6-2271082-0
CELLO,REC,96P,TH,V,FG,DIP4.0,CLIP

Customers Also Bought





TE Part #T4171120008-002
M12,REAR MOUNT,FEMALE, A, 8P, 0.5 M WIRE



TE Part #T2030001040-000
CEM-4.0



TE Part #4-2271928-0
CELLO,PIN,48P,TH,RA,FG,DIP3.0,-




TE Part #1-1903128-7
DYNAMIC 1100D TAB HSG 34P P/M



TE Part #T2050323201-002
HEEE-032-F



TE Part #T1871002201-000
HB-PLM-PM-BASE



TE Part #1-179276-5
DYNAMIC 3200 HDR ASSY 2P H



TE Part #T2030002040-000
CEF-4.0



TE Part #T0931006524-001
CODING-PIN-M3-TF-SELF-TAPPING



TE Part #T0931000423-001
CODING-PIN-M3-TM-SELF-TAPPING

Documents

Product Drawings

CELLO,PIN,96P,TH,RA,FG,DIP3.0,-

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2271013-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2271013-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2271013-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

4-2271013-0

PCB Mount Header, Right Angle, Board-to-Board, 96 Position, 2.54 mm [.1 in]
Centerline, Fully Shrouded, Gold Flash, Through Hole - Solder, Signal



Product Specification

English