



TE Internal #: 2081937-1
1.85mm Series Connector, Jack, 50 ohm, Screw, 67 GHz, Cable-to-Board, 1 Position, Printed Circuit Board, Board Mount, -55 – 125 °C [-67 – 257 °F]
[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **1.85mm Series**
RF Connector Style: **Jack**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Screw**
Operating Frequency: **67 GHz**

Features

Product Type Features

RF Interface	1.85mm Series
RF Connector Style	Jack
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Stainless Steel
Body Material Finish	Passivated



Contact Features

RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Beryllium Copper

Mechanical Attachment

RF Connector Coupling Mechanism	Screw
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical

Dimensions

Profile Height from PCB	11.18 mm[.437 in]
-------------------------	-------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
Operating Frequency	67 GHz

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Other

Dielectric Material	Polyetherimide (PEI)
---------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2016487-5 HF CA,1.85 M-M,70GHz,L1500	 TE Part # 2016487-3 HF CA,1.85 M-M,70GHz,L300	 TE Part # 2-2016487-0 HF CA,1.85 M TO M,70GHz,L2000	 TE Part # 1-2016487-0 HF CA,1.85 M-M,70GHz,L1000
 TE Part # 1-2016661-0 2.40 MALE-MALE,50G,L1000,WITH ARMOR	 TE Part # 1-2016489-0 HF CA,1.85 M-F,70GHz,L1000	 TE Part # 1-2016489-2 HF CA,1.85 M-F,70GHz,L1220	 TE Part # 2-2016489-0 HF CA,1.85 M TO F,70GHz,L2000
 TE Part # 2081551-1 ADAPTOR 2.4MM PLUG TO 1.85MM PLUG	 TE Part # 2081549-1 ADAPTOR 1.85MM PLUG TO 1.85MM PLUG	 TE Part # 2016487-9 HF CA,1.85 M-M,70GHz,L910	 TE Part # 2016489-9 HF CA,1.85 M-F,70GHz,L910
 TE Part # 1-2016489-5 HF CA,1.85 M-F,70GHz,L1500	 TE Part # 1-2016487-2 HF CA,1.85 M-M,70GHz,L1220	 TE Part # 2081552-1 ADAPTOR 2.4MM PLUG TO 1.85MM JACK	 TE Part # 1-2016659-0 1.85 F DOUBLE,67G,1.0M WITH ARMOR,BRAID



Customers Also Bought



Documents

Product Drawings

1.85MM JACK 2-HOLE FLANGE SOLDERLESS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2081937-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2081937-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2081937-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English