

MATERIALS AND FINISHES:

TYPICAL VSWR OF 1.5 TO 26 GHz

BODY: STAINLESS STEEL
PASSIVATED

OUTER CONTACT: BERYLLIUM COPPER
PLATED GOLD (10μ-in MIN) OVER
NICKEL (100μ-in MIN)




CENTER CONTACT: BERYLLIUM COPPER
PLATED GOLD (10μ-in MIN) OVER
NICKEL (100μ-in MIN)

INSULATOR: PTFE

SMA JACK
INTERFACE

SMP JACK
INTERFACE

.188 REF
[4.76]
ACROSS FLATS



73386-1430	TRAY
PART NO.	PACKAGING

MIL-STD-348B, FIG. 326.1			SMP INTERFACE	
MIL-STD-348B, FIG. 310.2			SMA INTERFACE	
SPECIFICATION			DESCRIPTION	
DOCUMENT STATUS	P1	RELEASE DATE	2018/05/17	18:09:14

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									