



Part Number : [190030048](#)
Product Description : InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Continuous Molded Strip, Tab 6.35 x 0.81mm
Series Number : 19003
Status : Active
Product Category : Quick Disconnects
Engineering Number : BB-2206XC



Documents & Resources

Drawings
[190030048_sd.pdf](#)

3D Models and Design Files
[190030048_stp.zip](#)

Specifications
[PS-19902-008-001.pdf](#)
[PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19003
Description	InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²), Continuous Molded Strip, Tab 6.35 x 0.81mm
Comments	Funnel Entry
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	800753029170

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.072/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	6.60mm max.
Wire Size (AWG)	14, 16
Wire Size mm²	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ACP Perishable Tool Kit used in ACP Presses that Process Continuous Molded Product	<u>190280045</u>
Mini-Mac Applicator	<u>638834100</u>