




番号 NO.	部品名 PART NAME	個数 QUAN.	材質 MATERIAL		仕上げ FINISH
1	プラグハウジング アッセンブリ PLUG HOUSING ASSEMBLY	1	アウターハウジング OUTER HOUSING	ガラス入りPBT G.F. PBT	—#—
			インナーハウジング INNER HOUSING	ガラス入りPBT G.F. PBT	—#—
			シールド SHIELD	鋼 STEEL	ニッケルメッキ NICKEL PLATING
			ターミナル TRMINAL	リン青銅 PHOS. BRO.	接点部 金 : 0.76 μm I N. CONTACT AREA , GOLD 圧接部 錫メッキ I.D.PORITION, TIN PLATING ニッケルメッキ NICKEL BASE
2	アッパーハウジング UPPER HOUSING	2	ガラス入りPBT G.F. PBT		—#—

注記 1. 適用電線: UL STYLE NO. 20276 相当品
NOTES APPLICABLE WIRE : FIT FOR UL STYLE NO. 20276

サイズ SIZE	導体 WIRE RANGE	絶縁体外径 INS. RANGE
AWG# 28	0.38 (7/0.127)	0.58

2. 本製品は 52316-***11 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52316-***11.

29.34	52316-3619		36
22.99	52316-2619	52316-***19	26
19.18	52316-2019		20
A	MATERIAL NO.	MODEL NO.	N 極数 極数 CKT.

REVISED EC NO: J2016-1045 DRWN: HTAKAHASHI 03/2016/02/25 CHKD: APPR: MYAGI 2016/04/06	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2.0	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION							
		0.25 UNDER	UNDER	± 0.2	DRAWN BY	DATE	TITLE 1.27 I/O PLUG ASSY									
		0.25 OVER	0.5 UNDER	± 0.2	H. KAWABATA	2004/04/27										
		0.5 OVER	1.0 UNDER	± 0.2	CHECKED BY	DATE	-LEAD FREE- molex									
		1.0 OVER	10 UNDER	± 0.2	K. TOJO	2004/04/27										
		10 OVER	30 UNDER	± 0.25	APPROVED BY		DATE		DOCUMENT NO. SD-52316-002							
		30 OVER		± 0.3												
		ANGULAR ±3 °			MATERIAL NO.		SHEET NO.									
					SEE CHART		1 OF 1									
		B	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								