



Part Number : [734151001](#)
Product Description : 50 Ohms, MMCX Right-Angle Jack, PCB, Gold (Au) Plated Body per Commercial Requirements, Tray
Series Number : 73415
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings
[734151001_sd.pdf](#)

3D Models and Design Files
[734151001_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73415
Description	50 Ohms, MMCX Right-Angle Jack, PCB, Gold (Au) Plated Body per Commercial Requirements, Tray
Product Name	MMCX
Style	PCB
Type	Microminiature
UPC	800755970708

Electrical

Frequency	6 GHz
Impedance	50 Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	0.436/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
--------------	----

Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

This document was generated on Mar 01, 2025