




Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**
Switch Contact Plating Material: **Gold**
Case Color: **Black**
Case Material: **Glass-Filled Polyester**
Sealed Device: **Yes**

Features

Product Type Features

DIP & SIP Switch Type	DIP
Sealed Device	Yes
Actuator Style	Recessed Rocker

Configuration Features

Number of Positions	5
Number of Switches	5
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	1.5 A
Operating Voltage	50 VDC

Body Features

Product Orientation	Vertical
Case Color	Black
Case Material	Glass-Filled Polyester

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Switch Contact Plating Material	Gold
Contact Base Material	Gold



Termination Features

Termination Post & Tail Length	3.56 mm[.135 in]
Termination Method to PCB	Through Hole - Solder

Housing Features

Low Profile	No
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Product Length	14.73 mm[.58 in]
Product Height	7.06 mm[.278 in]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
Packaging Quantity	21

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1375819-1
CST-100 II CONTACT TIN PLT



TE Part #6-1879215-3
CPF 0402 20K5 0.1% 25PPM 1K RL




TE Part #1-1825137-6
A103SYCQ04




TE Part #320559
PIDG SPLICE 22-16COMM 22-18MIL




TE Part #1375820-3
CST-100 II HOUSING 3 POS



TE Part #102128-2
MOD V RECP LP



TE Part #8-2176397-9
3502 4K7 1%



TE Part #184235-1
RECEPT,PIDG FASTON 16-14 187



TE Part #735159
250 PIDG FF

Documents

- CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-435626-2_BL.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-435626-2_BL.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-435626-2_BL.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English