




Switches > Toggle Switches



Contact Current Rating: **.4 A**
Configuration (Pole-Throw): **Single Pole - Double Throw**
Operating Function: **On On**
Number of Positions: **2**
Operating Voltage: **20 VDC**

Features

Product Type Features

Sealed Device	Yes
Switch Type	Rocker Switch

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On
Number of Positions	2

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VAC

Body Features

Product Orientation	Vertical
---------------------	----------

Contact Features

Switch Contact Plating Material	Gold
---------------------------------	------

Termination Features

--	--



Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Housing Features

Process Sealed	Yes
----------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought



TE Part #4-2176337-6
CRGCQ 0402 56K 1%

TE Part #5-2176337-3
CRGCQ 0402 220K 1%

TE Part #84953-8
1MM FPC HORZ.TOP CONT.ASSY 8P

TE Part #1-84953-6
1MM FPC HORZ.TOP CONT.ASSY 16P

TE Part #53123-2
TERMINAL,SOLIS SPR SPD 16-14 6

TE Part #2-2176337-9
CRGCQ 0402 2K2 1%

TE Part #92009-2
RCPT HSG,METRIC INTERCONN SYS

TE Part #1879350-6
RR01 5% R36 AMMO

TE Part #1623104-1
CRG0805 1% 11K

TE Part #6469028-1
HM-ZD 2PR RECP 40P

Documents

Product Drawings

RAS1R102VS2RES

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2267088-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2267088-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2267088-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Subminiature Switches

English