

OUAZ-SH-124L,900

 SUPERSEDED

OEG

TE Internal #: 4-1419145-8

TE Internal Description: OUAZ-SH-124L,900

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUN 2020 (209)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                           |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #7331-BCE-T-010-000  
10mBar Differential Sensor



TE Part #1825027-6  
FSMRA2JHA04=R/A,TACT PB SW,260



TE Part #6-1393144-6  
K10P-11D55-12=K10/K20



TE Part #745201-7  
09 HDE AP RECEPT, LEAD FREE



TE Part #2-1393250-2  
W28-XQ1A-0.75=W28

TE Part #63699-1  
ADAPTER 187 FASTON TPBR

TE Part #1-292161-1  
CT P/HDR ASSY V 11P W/KINK NAT

TE Part #1658623-7  
30 NOVO MIL 30DP, LEAD FREE

TE Part #1-640550-8  
18P MTA100 COVER

TE Part #1-1415899-6  
RZ03-1A4-D012

Documents

Product Drawings

OUAZ-SH-124L,900

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1419145-8\_E4.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1419145-8\_E4.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1419145-8\_E4.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

OUAZ series Relay data sheet English

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL



English