

-
- Home
 - Part Number Search
 - Document Search
 - CAD Model Search
 - Text Search
 - Alternate/Lead Free Part Search
 - Multiple Part Comparison
 - Alphabetical Search
 - Brand Search
 - Industry Product Search
 - Product Type Search
 - Product Family Search
 - Competitor Cross Reference
 - Lead Free Solutions
 - Tool Search
 - Help/Glossary

Sockets

DIP Sockets

AMP 540-AG11D Active Active

(Tyco Electronics P/N: 7-1437536-4)

Not ELV or RoHS Compliant
Search for Compliant (Leadfree)
Alternative
Search for Parts

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
General Info Sales Info Assembly Subcontractors	Pricing Product Availability	Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	Non-compliant
Lead Free Solder Process:	Reflow solder capable to 245°C
Product Type:	DIP Socket
No. of Positions:	40
Row-to-Row Spacing (mm [in]):	15.24 [0.600]
Contact Mount:	Thru Hole
Mount Style:	Vertical
Centerline (mm [in]):	2.54 [0.100]

Other Properties:	
Insulation Resistance (MΩ):	5,000
Contact Resistance (mΩ):	10
Sleeve Material:	Brass/Copper
Contact Termination Area Plating:	Gold
Product Series:	500 Series

Profile:	Standard
Frame Style:	Closed
Leg Style:	Straight
Contact Material:	Beryllium Copper
Contact Mating Area Plating:	Gold (25)
Contact Style:	Screw Machine
Mating Contact Type:	Four-Fingered
Height Above PC Board (mm [in]):	4.57 [0.180]
Temperature Range (°C):	125
Packaging Method:	Tube
Termination Post Length (mm [in]):	3.18 [0.125]

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contain component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

