



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.6% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2329359-9
PB ON/OFF HC GRE M1 TERM IP68
500MM LHS

TE Part #91368-1
PRO-C TL & DIE SL156 24-18

TE Part #4-2172070-2
M12.MALE.PNLREAR.ACODE.5P.
PCBSTAND.STRT

TE Part #1-282843-0
TERMI-BLOK PCB MOUNT 90 10P.

TE Part #2-2329328-0
PB OFF/ON HC BLU M4 TERM. IP68

TE Part #4-2176092-6
RP 2A 0.25W 2K15 0.1% 25PPM 1K RL

TE Part #1-282847-0
TERMI-BLOK PCB MOUNT 35 10P.

TE Part #282843-8
TERMI-BLOK PCB MOUNT 90 8P.1

TE Part #2-1623795-0
SQP10 R22 5% WIRE

TE Part #TAB62546501-040
M12B2-MS-FS-PUR TORSION-4.0M

Documents

Product Drawings

5182 2240 00

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1060498-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1060498-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1060498-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



RF Between Series Adapters

English