




Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **In-Series Adapter**

Body Orientation: **Straight**

Side A Interface: **4.3/10Series**

Side A Gender: **Jack**

Side B Interface: **4.3/10Series**

Features

Product Type Features

|                                  |                   |
|----------------------------------|-------------------|
| Connector Interface Adapter Type | In-Series Adapter |
| Side A Interface                 | 4.3/10Series      |
| Side A Gender                    | Jack              |
| Side B Interface                 | 4.3/10Series      |
| Side B Gender                    | Jack              |
| Connector System                 | Cable-to-Cable    |
| Sealable                         | No                |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 1 |
|---------------------|---|

Electrical Characteristics

|           |      |
|-----------|------|
| Impedance | 50 Ω |
|-----------|------|

Contact Features

|                                              |                  |
|----------------------------------------------|------------------|
| RF Connector Center Contact Material         | Beryllium Copper |
| RF Connector Center Contact Plating Material | Gold (Au)        |

Housing Features



|                  |          |
|------------------|----------|
| Body Orientation | Straight |
|------------------|----------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 85 °C[-40 – 185 °F] |
|-----------------------------|---------------------------|

Operation/Application

|                     |       |
|---------------------|-------|
| Operating Frequency | 6 GHz |
|---------------------|-------|

Product Compliance

For compliance documentation, visit the product page on TE.com>









|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                                                                                                                                                                                                                                                                                                                   |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                                                                                                                                                                                                                                                                                                                                                                                                            |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUL 2021 (219)<br>SVHC > Threshold:<br>Pb (4% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                         |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                                                                                                                                                                                                                                                                                                                  |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



|                                                                                                                                                             |                                                                                                                                                             |                                                                                                                                                             |                                                                                                                                                              |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 2016295-1<br/>ST PLUG TO RA PLUG CABLE ASSEMBLY 1/2SF</p>    |  <p>TE Part # 2016295-3<br/>C/A,ST PLUG TO RA PLUG,SCREW, 2M 1/2" SF</p>  |  <p>TE Part # 2016294-1<br/>C/A,ST PLUG TO ST PLUG,SCREW, 1M 1/2" SF</p> |  <p>TE Part # 2016296-6<br/>C/A,ST PLUG TO ST PLUG,HAND SCREW, 1M</p>     |
|  <p>TE Part # 1-2016294-6<br/>C/A,ST PLUG TO ST PLUG,SW, 0.3M 1 /2" S</p> |  <p>TE Part # 2016296-1<br/>C/A,ST PLUG TO ST PLUG,SCREW, 1M .250 CA</p> |  <p>TE Part # 2016298-6<br/>C/A,ST PLUG TO ST PLUG,HAND SCREW, 1M</p>   |  <p>TE Part # 2016298-1<br/>C/A,ST PLUG TO ST PLUG,SCREW, 1M .141 CA</p> |
|  <p>TE Part # 2081558-1<br/>ADAPTER N MALE TO 4.3-10 MALE</p>            |                                                                                                                                                             |                                                                                                                                                             |                                                                                                                                                              |

Customers Also Bought

|                                                                                                                                               |                                                                                                                                                             |
|-----------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part #1825255-5<br/>MHS12304=SPDT SL SW VERT AG</p> |  <p>TE Part #CAT-C339-T2201<br/>Wirewound Resistor: Mineral, 2.5 Kw</p> |
|-----------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|

Documents

- Product Drawings
- ADAPTER 4.3-10 FEMALE TO 4.3-10 FEMALE
- English
- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG\_CVM\_CVM\_2081554-1\_A.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_2081554-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2081554-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English