




PRO OFFICE SANO series ceiling lights are an efficient solution for renovating and modernising old T5/T8 louver lights. Due to slightly larger dimensions, the lights cover the old installations and so do not require the ceiling to be repainted.

Arrestor cables, plug connectors and mounting brackets make installation so easy that it can be performed by one person. In addition to ease of installation, the series offers impressive technical highlights: It provides flexible light control via CCT switch (3,000 K/4,000 K), dimmable variants (leading-edge/trailing-edge or DALI) and output adjustment in four stages (TRIAC variants only). They are also eligible for BEG German federal



#### Special features

- Renovation solution for T5/T8 louver lights
- Covers the old installation, therefore no repainting necessary
- Easy to install due to plug connector, arrestor cables and mounting bracket
- Light colour adjustable in two stages
- Output adjustable in four stages [TRIAC variants only]
- Eligible for BEG German federal funding for energy-efficient buildings
- Emergency power capable [176-280 V/DC EOFI: 95 %]

|                                              |                                                                                                |
|----------------------------------------------|------------------------------------------------------------------------------------------------|
| <b>Housing Material</b>                      | Aluminium, Stainless steel                                                                     |
| <b>Housing Color</b>                         | White                                                                                          |
| <b>Functions</b>                             | Leuchte kann mit Gleichstrom aus einer Zentralbatterie eines Notstromsystems betrieben werden. |
| <b>Protection Class</b>                      | Protection class I/protective grounding                                                        |
| <b>Protection Class Lamp</b>                 | Protection class III/safety extra-low voltage                                                  |
| <b>Power Selectable</b>                      | 27 W, 30 W, 32 W, 35 W                                                                         |
| <b>Rated Power Consumption Standby</b>       | 0.5 W                                                                                          |
| <b>Rated Input Voltage Frequency</b>         | 198-264 V/AC 50 / 60 Hz                                                                        |
| <b>Power Supply Unit incl.</b>               | Yes                                                                                            |
| <b>Dimmable</b>                              | Yes                                                                                            |
| <b>Control</b>                               | Trailing-edge dimmer, Leading-edge dimmer                                                      |
| <b>Motion Detector</b>                       | No                                                                                             |
| <b>Voltage range emergency lighting EOFI</b> | 176-280 V/DC<br>95 %                                                                           |
| <b>Light Source</b>                          | LED, Light source not changeable                                                               |
| <b>Color Temperature</b>                     | 3000/3500/4000 K                                                                               |
| <b>Colour Consistency</b>                    | 3 SDCM                                                                                         |
| <b>Colour Rendering Index (Ra)</b>           | 90                                                                                             |
| <b>Rated Luminous Flux</b>                   | 4350/4600/4500 lm                                                                              |
| <b>Rated Angle of Reflection UGR</b>         | 90 Degree<br>19                                                                                |
| <b>Length</b>                                | 1225 mm                                                                                        |
| <b>Width</b>                                 | 325 mm                                                                                         |
| <b>Height</b>                                | 48 mm                                                                                          |
| <b>Working Temperature</b>                   | -10 to 40 °C                                                                                   |

|                            |              |
|----------------------------|--------------|
| <b>Storage Temperature</b> | -10 to 40 °C |
| <b>IP Protection Class</b> | IP 40        |
| <b>Life Time L70 / B50</b> | 50000 h      |
| <b>Life Time L80 / B20</b> | 50000 h      |
| <b>Switching Cycles</b>    | 100000       |
| <b>EEL</b>                 | F            |

